



## Serie 525 >INCH<

**Gelenkköpfe Maßreihe K**  
**Gleitpaarung: Stahl auf PTFE**  
**wartungsfrei**  
**Außengewinde**  
**Höchste Belastungen**  
**Erhöhter Korrosionsschutz**

### Innenring:

Wälzlagerstahl, gehärtet, geschliffen und poliert; Gleitoberfläche hartverchromt

### Außenring:

Edelstahl, ausgekleidet mit einer Gleitfolie bestehend aus PTFE mit Metallgewebe

### Gehäuse:

Hochfester Stahl, geschmiedet, gleitgeschliffen und galvanisch beschichtet

### Lagerluft:

Reduzierte Lagerluft

Wartungs- und Bedienungsanleitung unter [www.askubal.de/service/bedienungs-und-wartungsanleitungen/](http://www.askubal.de/service/bedienungs-und-wartungsanleitungen/)



## Series 525 >INCH<

**Rod ends dimension series K**  
**Mating materials: Steel on PTFE**  
**Maintenance-free**  
**Male thread**  
**Highest loads**  
**Increased corrosion protection**

### Inner ring:

Antifriction bearing steel, hardened, ground and polished, sliding face hard chromium plated

### Outer ring:

Stainless steel, lined with an antifriction film consisting of PTFE with metal fabric

### Housing:

High strength steel, forged, vibratory finished and electroplated

### Bearing clearance:

Reduced bearing clearance

Instruction and maintenance manual see [www.askubal.de/en/service/instruction-and-maintenance-manual/](http://www.askubal.de/en/service/instruction-and-maintenance-manual/)