



Serie 326

Gelenklager Baureihe S
Maßreihe K
Gleitpaarung: Stahl auf Stahl
wartungspflichtig
Höchste Belastungen

Innenring:

Wälzlagerstahl, gehärtet, geschliffen und poliert; Gleitoberfläche hartverchromt

Außenring:

Gelenklageraußenring aus Vergütungsstahl, brüniert, spanlos um den Innenring geformt, Außendurchmesser geschliffen

Schmierung:

Die Schmierstoffversorgung erfolgt über die Schmiernut im Außenring.

Lagerluft:

Reduzierte Lagerluft

Wartungs- und Bedienungsanleitung unter www.askubal.de/service/bedienungs-und-wartungsanleitungen/



Series 326

Spherical bearings version S
Dimension series K
Mating materials: Steel on steel
Maintenance required
Highest loads

Inner ring:

Antifriction bearing steel, hardened, ground and polished, sliding face hard chromium plated

Outer ring:

Outer ring of spherical bearing made of tempering steel, bronzed, swaged around the inner ring, outside diameter ground

Lubrication:

The lubricant enters the lubrication groove through a cross hole in the outer ring.

Bearing clearance:

Reduced bearing clearance

Instruction and maintenance manual see www.askubal.de/en/service/instruction-and-maintenance-manual/