



Gelenklager Sonderausführung
Gleitpaarung: Stahl auf PTFE
wartungsfrei
Ausführung S abgedichtet (-DRS)

Innenring:
Wälzlagerstahl, gehärtet, geschliffen und gefinished.

Außenring:
Stahl, ausgekleidet mit PTFE.

Gummikappen:
Synthetischer Gummi.

Toleranzen:
Nach DIN ISO 12240-1; Maßreihe K, ausgenommen: d = H8; B = +/- 0,3.

Hinweis:
Bei diesen Gelenklagern ist zu beachten, dass der in der Tabelle angegebene Kippwinkel weder bei der Montage noch beim Betrieb überschritten wird, da sonst die Gummikappen beschädigt werden könnten.

Wartungs- und Bedienungsanleitung unter www.askubal.de/service/bedienungs-und-wartungsanleitungen/



Spherical bearing Special version
Mating materials: Steel on PTFE
Maintenance free
Version S sealed (-DRS)

Inner ring:
Antifriction bearing steel, hardened, ground and polished.

Outer ring:
Steel lined with an antifriction film, consisting PTFE.

Rubber bellows:
Synthetic rubber.

Tolerances:
Acc. to DIN ISO 12240-1, schedule K, except: d = H8; B = +/- 0,3.

Note:
With these rod ends, it is important to ensure that the tilt angle specified in the table is not exceeded, either while mounting or during operation, otherwise the rubber bellows may be damaged.

Instruction and maintenance manual see www.askubal.de/en/service/instruction-and-maintenance-manual/