



Gelenklager Sonderausführung
Gleitpaarung: Stahl auf PTFE
wartungsfrei
Ausführung S (-D)

Innenring:
Wälzlagerstahl, gehärtet, geschliffen und gefinished.

Außenring:
Stahl ausgekleidet mit PTFE,
Außendurchmesser geschliffen.

Außenteil:
Stahl, Außendurchmesser geschliffen.
Gelenklager wird in das Außenteil gepresst und beidseitig gegen axiales Verschieben gesichert. Dennoch ist beim Einbau darauf zu achten, dass beide Außenringe axial abgestützt werden.

Wartungs- und Bedienungsanleitung unter www.askubal.de/service/bedienungs-und-wartungsanleitungen/



Spherical bearing Special version
Mating materials: Steel on PTFE
Maintenance free
Version S (-D)

Inner ring:
Antifriction bearing steel, hardened, ground and polished.

Outer ring:
Steel lined with an antifriction film, consisting of PTFE, outer diameter ground.

Outer case:
Steel, outer diameter ground. Spherical bearing is pressed into the outer case and secured at both sides against axial movement. However the two outer rings should be axial supported at mounting.

Instruction and maintenance manual see www.askubal.de/en/service/instruction-and-maintenance-manual/