

# Floor Standing Steel Range Accessories

## Split bottom plate stainless steel, CBPS

- Description:** Fitted in place of the standard one piece bottom plate, allows direct cable entry. To achieve perfect sealing around the cables use the gasket kit BG01.
- Material:** AISI 304 / AISI 316L pre-grained stainless steel.
- Bottom plates:** 1.5 mm.
- Finish:** 240s pre-grained stainless steel (0.5 microns average).
- Pack quantity:** 1 kit of two part bottom plate.



For enclosure			
W	D		Item no.
600	400		CBPS0640
600	400		CBPS0640-316
600	500		CBPS0650
600	500		CBPS0650-316
600	600		CBPS0660
600	600		CBPS0660-316
800	400		CBPS0840
800	400		CBPS0840-316
800	500		CBPS0850
800	500		CBPS0850-316
800	600		CBPS0860
800	600		CBPS0860-316
1000	400		CBPS1040
1000	400		CBPS1040-316
1000	500		CBPS1050
1000	500		CBPS1050-316
1000	600		CBPS1060
1000	600		CBPS1060-316

For enclosures 1200 mm & 1600 mm wide use 2 x 600 mm & 2 x 800 mm wide bottom plates.

## Top cover with cable gland opening, CRG

- Description:** Roof plate with gland plates for cable entry.
- Material:** 1.5 mm steel plate.
- Finish:** RAL 7035 structured powder coating.
- Pack quantity:** 1 piece with gland plates, gaskets and mounting accessories.



For enclosure				
W	D	Openings	Gland opening	Item no.
600	600	1	310x96	CRG0606R5
600	800	1	310x96	CRG0608R5
800	600	2	210x96	CRG0806R5
800	800	2	210x96	CRG0808R5