

## Ventilated top cable cover, CRB

- Description:** For cable entry on three sides in combination with ventilation. Cable openings provided with brushes. To mount closing plates DFC or inside mounting of (maximum 4) DFN01 ventilation fans.
- Material:** 1.5 mm steel plate.
- Finish:** RAL 7035 structured powder coating.
- Pack quantity:** 1 piece with brushes and mounting accessories.
- Mounting requirement:** Add DFN ventilation fans or DFC closing plates.



For enclosure			
W	D	N° of cut outs	Item no.
600	600	4	CRB0606R5
600	800	6	CRB0608R5
800	600	4	CRB0806R5
800	800	6	CRB0808R5

## Raised side door, DNSR

- Description:** A 200 mm wide cover with cable entrances in top and bottom. Supplied with one gland plate and gasket. Hole pattern equals enclosure's frame to mount cable fixing bars.
- Material:** 1.75 mm steel plate.
- Finish:** RAL 7035 structured powder coating.
- Protection:** Complies with IP 33 | TYPE 1 with MM connector plate and gasket SPDG01. Door frame optional.
- Mounting requirement:** Add a separation plate SPD or marshalling plate MM to mount connectors and separate the side compartment.
- Pack quantity:** 1 piece with mounting accessories.



Item no.
DNSR2005R5
DNSR2006R5