

Thermal Management

Control Range

Accessories

Fix Thermostat, EFR

- Description:** Pre-set thermostats to manage temperature in panels. Sensor element thermostatic bimetal. Red one (EFR202) with a normally closed contact for regulating heaters. Blue one (EFR201) with a normally opened contact for regulating cooling devices or signal devices. Mounting clip for 35 mm DIN rail (EN 60715).
- Material:** Plastic according to UL94 V-0.
- Switch capacity:** 250V AC, 5 (1.6)A. 120V AC, 10 (2) A. 24V DC, 30W. Value in brackets for inductive load. Max. starting current of 16 A (AC) for 10 seconds.
- Operating temperature:** -40 to +80°C.
- Service life:** > 100,000 cycles.
- Connection:** 2 pole terminal for 2.5 mm², torque 0.8Nm max.
- Protection:** IP 20.
- Approvals:** CE, EAC, cULus_UL Listed.
- Finish:** Light grey.
- Pack quantity:** 1 piece.



Description	Pre-set (°C)	Item no.
Normally opened contact	35	EFR201
Normally closed contact	5	EFR202

