

Wall Mounted Steel Range Accessories

Display aluminium panel, ACA/ACB

- Description:** For controls, meters, indication lamps etc. The mounted components are protected by a 23.5 mm high frame. The aluminium panel is 3 mm thick and can be removed for drilling or screen printing. The double-bit 3 mm lock can be replaced by any optional insert or handle.
- Material:** Aluminium.
- Finish:** Anodised aluminium.
- Protection:** Complies with IP 54.
- Pack quantity:** 1 door with mounting accessories.

For enclosure		Viewing area		N° of locks	Item no.
H	W	h	w		
300	300	226	226	1	ACA03030
400	300	326	226	1	ACA04030
400	400	326	326	1	ACA04040
400	600	326	526	1	ACA04060
500	300	426	226	1	ACA05030
500	400	426	326	1	ACA05040
500	500	426	426	1	ACA05050
600	400	522	322	2	ACB06040
600	600	522	522	2	ACB06060
600	800	522	722	2	ACB06080
700	500	622	422	2	ACB07050
800	600	722	522	2	ACB08060
800	800	722	722	2	ACB08080
1000	600	922	522	2	ACB10060
1000	800	922	722	2	ACB10080
1200	600	1122	522	2	ACB12060
1200	800	1122	722	2	ACB12080

