

Inner doors, ADI

| | |
|-----------------------|---|
| Description: | For controls, meters, lamps, etc. Hinges can be mounted to allow left or right hand opening. Lock double-bit 3 mm insert; 700 mm high doors and above have 2 locks. Usable depth between inner and external door: 35 mm. Adjustable depth position with AMG accessory. Workable area: H-55, W- 108. 19" version available on request. Machining is required for stainless steel enclosures. |
| Material: | Door 1.5 mm mild steel, vertical top and bottom profiles 2 mm mild steel. |
| Finish: | RAL 7035 structure powder coating. |
| Protection: | IP 2X. |
| Pack quantity: | Inner door, two vertical top and bottom profiles and mounting accessories. |

| For enclosure | | Inner door dimensions | | N° of locks | Item no. |
|---------------|-----|-----------------------|-----|-------------|------------|
| H | W | h | w | | |
| 400 | 300 | 345 | 192 | 1 | ADI04030R5 |
| 400 | 400 | 345 | 292 | 1 | ADI04040R5 |
| 400 | 500 | 345 | 392 | 1 | ADI04050R5 |
| 400 | 600 | 345 | 492 | 1 | ADI04060R5 |
| 500 | 300 | 445 | 192 | 1 | ADI05030R5 |
| 500 | 400 | 445 | 292 | 1 | ADI05040R5 |
| 500 | 500 | 445 | 392 | 1 | ADI05050R5 |
| 600 | 400 | 545 | 292 | 1 | ADI06040R5 |
| 600 | 500 | 545 | 392 | 1 | ADI06050R5 |
| 600 | 600 | 545 | 492 | 1 | ADI06060R5 |
| 600 | 800 | 545 | 692 | 1 | ADI06080R5 |
| 700 | 500 | 645 | 392 | 2 | ADI07050R5 |
| 800 | 400 | 745 | 292 | 2 | ADI08040R5 |
| 800 | 600 | 745 | 492 | 2 | ADI08060R5 |
| 800 | 800 | 745 | 692 | 2 | ADI08080R5 |
| 1000 | 600 | 945 | 492 | 2 | ADI10060R5 |
| 1000 | 800 | 945 | 692 | 2 | ADI10080R5 |
| 1200 | 600 | 1145 | 492 | 2 | ADI12060R5 |
| 1200 | 800 | 1145 | 692 | 2 | ADI12080R5 |

