


MCSL-PD

Combinable enclosure | Power Distribution



IP 44,55 | TYPE 12 | IK 10

The mild steel combinable floor standing enclosure range, MCSL, is available off the shelf in many different sizes, and is ideal for power distribution applications. The front opening can be segregated with partial panels or doors to meet power distribution system requirements. Only parts required will be delivered, which means full flexibility, lower costs, and greater procurement efficiency will be achieved.

Material: Frame: 1.5 painted steel. Rear and roof panels: 1.5 mm painted steel.

Frame: Seam welded reversed open profiles with 25 mm hole pattern according to DIN 43660. Including integrated external hole pattern.

Rear panel: Fitted by M6 torx screws. Standard facilities for rear door mounting.

Roof panel: Removable.

Earthing: All panels are earthed through their fittings and are equipped with a separate earthing stud.

Finish: RAL 7035 structured powder coating.

Protection: IP 44, 55 | TYPE 12 | IK 10, depending of doors configuration.

Mounting requirements: Standard delivery ready for combined installation. For stand-alone installation add side panels.

Delivery: Frame, rear and roof panel. Delivery also includes earthing bolts. Delivered on a pallet with identical width of the enclosure to allow suiting without removal. All packing material is recyclable.

MCSL-PD

Combinable enclosure | Power Distribution



CONNECT AND PROTECT

Enclosure dimensions				
H	W	D	Item no.	
1800	400	600	MCSL18046R5	
1800	400	800	MCSL18048R5	
1800	600	400	MCSL18064R5	
1800	600	600	MCSL18066R5	
1800	600	800	MCSL18068R5	
1800	800	400	MCSL18084R5	
1800	800	600	MCSL18086R5	
1800	800	800	MCSL18088R5	
1800	1000	400	MCSL18104R5	
1800	1000	600	MCSL18106R5	
1800	1000	800	MCSL18108R5	
1800	1200	400	MCSL18124R5	
1800	1200	600	MCSL18126R5	
1800	1200	800	MCSL18128R5	
2000	400	600	MCSL20046R5	
2000	400	800	MCSL20048R5	
2000	600	400	MCSL20064R5	
2000	600	600	MCSL20066R5	
2000	600	800	MCSL20068R5	
2000	800	400	MCSL20084R5	
2000	800	600	MCSL20086R5	
2000	800	800	MCSL20088R5	
2000	1000	400	MCSL20104R5	
2000	1000	600	MCSL20106R5	
2000	1000	800	MCSL20108R5	
2000	1200	400	MCSL20124R5	
2000	1200	600	MCSL20126R5	
2000	1200	800	MCSL20128R5	
2200	400	600	MCSL22046R5	
2200	400	800	MCSL22048R5	
2200	600	600	MCSL22066R5	
2200	600	800	MCSL22068R5	
2200	800	600	MCSL22086R5	
2200	800	800	MCSL22088R5	
2200	1000	600	MCSL22106R5	
2200	1000	800	MCSL22108R5	
2200	1200	600	MCSL22126R5	
2200	1200	800	MCSL22128R5	

MCSL-PD

Combinable enclosure | Power Distribution



CONNECT AND PROTECT