

Mounting profiles, CLPF

Description: The CLPF profile system is a 40 mm wide and 25 mm high profile, which can be mounted in all directions on the enclosure's frame. It can also be used in combination with the CLPK and the VB profiles. By turning the profile it can be used as a standard CP20/40 profile in combination with GLM 40/6 sliding nuts, to mount installation material which needs adjusting in depth. The profiles, when mounted onto the enclosure's frame are flush with the enclosure's profiles. Two rows of hole patterns for cage nut fixing and self tapping screws are provided. For 90 mm wide profiles two profiles can be mounted next to each other.

Material: Zinc plated steel.

Pack quantity: 4 profiles including fixing accessories.

For enclosure				
H/W	W/D	Max. loading Horizontal C	Max. loading Horizontal □	Item no.
400	400	800 N	1000 N	CLPF400
600	600	800 N	1000 N	CLPF600
800	800	800 N	1000 N	CLPF800
1000	1000	800 N	1000 N	CLPF1000



Fix system vertical profiles, MSFP

Description: Vertical profiles to build up fix systems. It can be mounted with or without sidepanels MSPS. These profiles lets us to mount MCCBs in mounting plates MSMPN, or DIN rails for modular components with the accessory fix MSADP or adjustable MSMPA01. The busbar supports in the rear of the compartments, MSFH, mount directly to the profile.

Material: 1.55 mm galvanized steel.

Delivery: 2 pieces with mounting material.

For enclosure	
H	Item no.
1800	MSFP1800
2000	MSFP2000
2200	MSFP2200

