


# SECHSKANTMUTTER MIT BUND, DIN 6331

## SCHEIBE DIN 6340



**2140.33.**



**Werkstoff:**

vergütet, Festigkeitsklasse 10.9

**Ausführung:**

gedreht und gefräst

**Hinweis:**


Gewindelänge 1,5 x M

**2140.33. Sechskantmutter mit Bund, DIN 6331**

Bestell-Nummer	M	a	d <sub>1</sub>	e	m	s
2140.33.08	M8	3,5	18	15	12	13
2140.33.10	M10	4	22	18,4	15	16
2140.33.12	M12	4	25	20,7	18	18
2140.33.14	M14	4,5	28	24,2	21	21
2140.33.16	M16	5	31	27,7	24	24
2140.33.18	M18	5	34	31,2	27	27
2140.33.20	M20	6	37	34,6	30	30
2140.33.22	M22	6	40	39,2	33	34
2140.33.24	M24	6	45	41,5	36	36
2140.33.30	M30	6	58	53,1	45	46



**2140.34.**



**Werkstoff:**

vergütet, Festigkeit 1200-1400 N/mm<sup>2</sup>

**2140.34. Scheibe DIN 6340**

Bestell-Nummer	M	d <sub>1</sub>	d <sub>2</sub>	s
2140.34.08	M8	8,4	23	4
2140.34.10	M10	10,5	28	4
2140.34.12	M12	13	35	5
2140.34.14	M14	15	40	5
2140.34.16	M16	17	45	6
2140.34.18	M18	19	45	6
2140.34.20	M20	21	50	6
2140.34.22	M22	23	50	8
2140.34.24	M24	25	60	8
2140.34.30	M30	31	68	10