


SCHEIBE


244.10.



244.10. Scheibe

Bestell- Nummer	d_1	d_2	s_1	Bestell- Nummer	d_1	d_2	s_1
244.10.064.017.03	6.4	17	3	244.10.204.030.05	20.4	30	5
244.10.084.016.04	8.4	16	4	244.10.210.042.06	21	42	6
244.10.084.017.03	8.4	17	3	244.10.210.042.08	21	42	8
244.10.084.023.04	8.4	23	4	244.10.210.044.08	21	44	8
244.10.085.020.04	8.5	20	4	244.10.210.045.08	21	45	8
244.10.090.026.04	9	26	4	244.10.210.045.16	21	45	16
244.10.105.020.04	10.5	20	4	244.10.210.046.06	21	46	6
244.10.105.025.04	10.5	25	4	244.10.210.049.06	21	49	6
244.10.105.025.05	10.5	25	5	244.10.210.050.10	21	50	10
244.10.105.026.04	10.5	26	4	244.10.210.065.08	21	65	8
244.10.105.028.04	10.5	28	4	244.10.210.070.12	21	70	12
244.10.105.030.05	10.5	30	5	244.10.220.065.12	22	65	12
244.10.110.030.06	11	30	6	244.10.220.068.12	22	68	12
244.10.110.036.06	11	36	6	244.10.230.038.07	23	38	7.5
244.10.125.028.04	12.5	28	4	244.10.250.042.09	25	42	9
244.10.130.024.05	13	24	5.5	244.10.250.046.10	25	46	10
244.10.130.030.05	13	30	5	244.10.250.055.10	25	55	10
244.10.130.035.05	13	35	5	244.10.250.056.10	25	56	10
244.10.130.030.06	13	30	6	244.10.250.065.12	25	65	12
244.10.130.035.08	13	35	8	244.10.250.070.10	25	70	10
244.10.130.046.08	13	46	8	244.10.250.090.12	25	90	12
244.10.134.023.04	13.4	23	4	244.10.260.058.06	26	58	6
244.10.135.026.05	13.5	26	5	244.10.260.070.12	26	70	12
244.10.164.026.04	16.4	26	4	244.10.260.080.12	26	80	12
244.10.170.030.06	17	30	6	244.10.290.050.08	29	50	8
244.10.170.034.06	17	34	6	244.10.310.068.08	31	68	8
244.10.170.035.04	17	35	4	244.10.310.068.10	31	68	10
244.10.170.035.06	17	35	6	244.10.310.080.12	31	80	12
244.10.170.036.04	17	36	4	244.10.310.100.15	31	100	15
244.10.170.036.13	17	36	13	244.10.320.090.15	32	90	15
244.10.170.037.06	17	37	6	244.10.320.092.15	32	92	15
244.10.170.038.06	17	38	6	244.10.370.060.08	37	60	8
244.10.170.040.06	17	40	6	244.10.370.080.08	37	80	8
244.10.170.050.06	17	50	6	244.10.430.092.08	43	92	8
244.10.170.050.10	17	50	10				
244.10.170.058.10	17	58	10				

Einbaubeispiel



Werkstoff:
C 45 vergütet