



LÍCOVANÝ ŠROUB



Příklad montáže



244.17.



Materiál:

Zušlechtěná ocel,
zušlechtěná na 12.9 ISO 898-1.

Provedení:

d₁ broušený,
vroubkovaná hlava.

244.17. Lícovaný šroub

d ₁	6	8	10	12	16	20	24
d ₂	M5	M6	M8	M10	M12	M16	M20
Úťahovací moment šroubů [Nm]	7	13	32	65	120	290	500
d ₃	10	13	16	18	24	30	36
h	4,5	5,5	7	9	11	14	16
s	3	4	5	6	8	10	12
l ₂	9,5	11	13	16	18	22	27
l ₁							
10	●	●					
12	●	●					
16	●	●		●			
20	●	●	●	●			
25	●	●	●	●	●		
30	●	●	●	●	●	●	
35	●	●	●	●	●	●	
40	●	●	●	●	●	●	●
45			●	●	●	●	●
50		●	●	●	●	●	●
55			●	●	●	●	●
60			●	●	●	●	●
65			●	●	●	●	●
70			●	●	●	●	●
80			●	●	●	●	●
90				●	●	●	●
100				●	●	●	●
120					●	●	●

Příklad objednávky:

Lícovaný šroub = 244.17.
 Jmenovitý průměr d₁ 12 mm = 120.
 Délka vedení l₁ 55 mm = 055
 Objednáací číslo = 244.17.120.055