


# LISTWA ŚLIZGOWA, BRĄZ Z WKŁADKAMI GRAFITOWYMI, VDI 3357


2961.74.



2961.74. Listwa ślizgowa, Brąz z wkładkami grafitowymi, VDI 3357

Numer katalogowy	Typ	b	s	a	b <sub>2</sub>	b <sub>1</sub>	d	e	e <sub>1</sub>	e <sub>2</sub>	Liczba śruby
2961.74.035.10.160	A	35	10	160	10	20	11	70	-	45	2
2961.74.035.10.200	A	35	10	200	10	20	11	110	-	45	2
2961.74.035.10.250	B	35	10	250	10	20	11	80	-	45	3
2961.74.045.15.160	A	45	15	160	15	30	13,5	70	-	45	2
2961.74.045.15.200	A	45	15	200	15	30	13,5	110	-	45	2
2961.74.045.15.250	B	45	15	250	15	30	13,5	80	-	45	3
2961.74.055.15.160	A	55	15	160	20	35	17,5	70	-	45	2
2961.74.055.15.200	A	55	15	200	20	35	17,5	110	-	45	2
2961.74.055.15.250	B	55	15	250	20	35	17,5	80	-	45	3
2961.74.075.25.160	A	75	25	160	25	40	17,5	70	-	45	2
2961.74.075.25.200	A	75	25	200	25	40	17,5	110	-	45	2
2961.74.075.25.250	B	75	25	250	25	40	17,5	80	-	45	3
2961.74.085.28.240	B	85	28	240	30	60	22	95	-	25	3
2961.74.085.28.300	D	85	28	300	30	60	22	85	80	25	4
2961.74.085.28.350	D	85	28	350	30	60	22	100	100	25	4
2961.74.085.28.400	D	85	28	400	30	60	22	115	120	25	4
2961.74.085.28.450	C	85	28	450	30	60	22	100	100	25	5
2961.74.085.30.160	A	85	30	160	30	60	22	70	-	45	2
2961.74.085.30.200	A	85	30	200	30	60	22	110	-	45	2
2961.74.085.30.250	B	85	30	250	30	60	22	80	-	45	3
2961.74.085.30.300	B	85	30	300	30	60	22	105	-	45	3
2961.74.085.30.350	B	85	30	350	30	60	22	130	-	45	3
2961.74.085.30.400	C	85	30	400	30	60	22	80	75	45	5
2961.74.100.25.160	A	100	25	160	30	60	17,5	70	-	45	2
2961.74.100.25.200	A	100	25	200	30	60	17,5	110	-	45	2
2961.74.100.25.250	B	100	25	250	30	60	17,5	80	-	45	3
2961.74.100.25.400	C	100	25	400	30	60	17,5	80	75	45	5
2961.74.100.30.160	A	100	30	160	30	60	22	70	-	45	2
2961.74.100.30.200	A	100	30	200	30	60	22	110	-	45	2
2961.74.100.30.250	B	100	30	250	30	60	22	80	-	45	3
2961.74.100.30.400	C	100	30	400	30	60	22	80	75	45	5
2961.74.125.25.160	A	125	25	160	30	75	17,5	70	-	45	2
2961.74.125.25.200	A	125	25	200	30	75	17,5	110	-	45	2
2961.74.125.25.250	B	125	25	250	30	75	17,5	80	-	45	3
2961.74.125.25.300	D	125	25	300	30	80	26	85	80	25	4
2961.74.125.25.350	D	125	25	350	30	80	26	100	100	25	4
2961.74.125.25.400.1	D	125	25	400	30	80	26	115	120	25	4
2961.74.125.25.400	C	125	25	400	30	75	17,5	80	75	45	5
2961.74.125.25.450	C	125	25	450	30	80	26	100	100	25	5
2961.74.125.25.500	C	125	25	500	30	80	26	110	115	25	5
2961.74.125.30.160	A	125	30	160	30	75	22	70	-	45	2
2961.74.125.30.200	A	125	30	200	30	75	22	110	-	45	2
2961.74.125.30.250	B	125	30	250	30	75	22	80	-	45	3
2961.74.125.30.300	B	125	30	300	30	75	22	105	-	45	3
2961.74.125.30.350	B	125	30	350	30	75	22	130	-	45	3
2961.74.125.30.400	C	125	30	400	30	75	22	80	75	45	5
2961.74.125.30.450	C	125	30	450	30	75	22	80	95	50	5
2961.74.125.30.500	C	125	30	500	30	75	22	80	120	50	5

Przykład zabudowy



**Material:**

Brąz z wkładkami grafitowymi, nie wymaga stałej konserwacji

**Uwaga:**

Śruby nie wchodzą w zakres dostawy.

**Mocowanie:**

Stosować śruby z łbem walcowym  
DIN EN ISO 4762.