



# SÜRTÜNME PLAKASI, BRONZ KENDİNDEN YAĞLAMALI, CNOMO

2962.78.45.



2962.78.45.



## 2962.78.45. Sürtünme Plakası, Bronz Kendinden Yağlamalı, CNOMO

Sipariş No.	Şekil	a	l	b	c	c <sub>1</sub>	c <sub>2</sub>	d	e	f	g	h	h <sub>1</sub>	h <sub>2</sub>	Vida Deliği Havşa Başlı	Vida Deliği adedi
2962.78.45.050.16.063	A	50	63	15	35	-	-	-	-	-	-	12	51	-	2	-
2962.78.45.050.16.160	C	50	160	19	31	-	-	-	-	-	-	21	147	-	2	-
2962.78.45.050.16.250	D	50	250	19	31	-	-	-	-	-	-	21	121	237	3	-
2962.78.45.080.16.160	C	80	160	22	58	-	-	68	15	145	-	31	147	-	2	2
2962.78.45.080.16.250	D	80	250	22	58	-	-	68	25	105	235	21	121	237	3	3
2962.78.45.100.16.063	B	100	63	15	33	67	85	-	-	-	-	12	51	-	4	-

### Malzeme:

Bronz Kendinden Yağlamalı

### Not:

Civatalar dahil değildir.

### Sabitleme:

Soket başlı vida kullanınız

DIN EN ISO 4762 M8.