



Max. load capacity according to DIN EN 13155/WLL
 Max. load capacity with stopper: 400kg
 Max. load capacity without stopper: 80kg
 Disk Ø: 400-1000mm
 Flat material dimensions: 2000x1000mm

Schutzvermerk nach DIN ISO 16016 beachten! Nachdruck nur mit unserer Genehmigung! All rights reserved according to DIN ISO 16016! Reprint with our permission only!					tolerance	material:	weight: 31.00 kg
					ISO 7168 M	drawing no.: 0013629	
				date	name	description: FX-HV400	
				drawn 18.03.2021	FEU		
				edit 15.02.2024			
				appr. 15.02.2024	TW		
				 www.flraig-te.de		part no.:	sheet 1 / 1
						11030402	A3
02	Green Dot	01.02.2024	TW			scale: 1:7	Status: Freigegeben
rev.	change	date	name				