

Halfen Plain Back Channel

MT 04E Framing Channel and Accessories

HM COLD ROLLED CHANNEL

HM 20/12



HM 26/18



HM 26/26



HM 28/12



HM 28/15




HM 28/28




HM 35/50




HM 36/20




HM 36/36




HM 38/17




HM 40/25




HM 49/30




HM 50/40



HM 54/33



HZM 41/22



Product diam	Weight (kg)		Order code 0280.	Price (£/ea)	Metre rate (£)	Cutting charge (£)
Material: Black (WB) (Black mild steel)						
HM 20/12 - 6000	3.080	A	030-00001			
HM 28/12 - 6000	5.220	A	260-00001			
HM 28/15 - 6070	6.250	A	010-00001			
HM 28/28 - 6000	8.100	A	050-00001			
HM 36/20 - 6000	8.300	B	240-00001			
HM 36/36 - 6000	12.960	B	070-00001			
HM 38/17 - 6070	10.350	A	020-00001			
HM 40/25 - 6070	12.650	A	230-00001			
HM 49/30 - 6070	18.210	A	220-00001			
HM 50/40 - 6000	20.400	B	090-00002			
HM 54/33 - 6070	29.700	A	280-00001			

Material: HDG (fv) (Hot dipped galvanised)						
HM 20/12 - 6000	4.000	B	030-00003			
HM 28/12 - 6000	5.700	B	260-00002			
HM 28/15 - 6070	6.980	A	010-00002			
HM 28/28 - 6000	8.700	B	050-00002			
HM 36/20 - 6000	9.200	B	240-00002			
HM 36/36 - 6000	13.200	B	070-00002			
HM 38/17 - 6070	10.600	B	020-00002			
HM 40/25 - 6070	12.900	B	230-00002			
HM 49/30 - 6070	18.800	B	220-00002			
HM 50/40 - 6000	20.700	B	090-00003			
HM 54/33 - 6070	29.700	B	280-00002			

Material: PG (sv) (Pre-galvanised)						
HM 26/18 - 6000	4.000	B	270-00001			
HM 26/26 - 6000	4.000	B	040-00001			
HM 28/28 - 6000	7.600	B	050-00003			
HM 35/50 - 6000	13.800	B	250-00001			

Material: SSA2/304 (Stainless steel)						
HM 20/12 - 6000	3.080	A	030-00002			
HM 28/15 - 6070	6.560	A	010-00004			
HM 38/17 - 6070	10.150	A	020-00003			
HM 40/25 - 6070	12.630	A	230-00003			
HM 49/30 - 6070	18.210	A	220-00003			

Material: SSA4/316 (Stainless steel)						
HM 28/15 - 6070	6.570	B	010-00003			
HM 28/28 - 6000	7.600	B	050-00004			
HM 36/36 - 6000	12.960	B	070-00003			
HM 38/17 - 6070	10.510	A	020-00004			
HM 40/25 - 6070	12.630	B	230-00004			
HM 49/30 - 6070	17.800	B	220-00004			
HM 50/40 - 6000	20.530	B	090-00001			
HM 54/33 - 6070	29.700	A	280-00003			

Material: Black (WB) (Black mild steel)						
			0284.			
HZM 41/22 - 6070	11.900	A	020-00001			

Material: HDG (fv) (Hot dipped galvanised)						
HZM 41/22 - 6070	12.570	B	020-00002			

Material: SSA4/316 (Stainless steel)						
HZM 41/22 - 6070	12.570	A	020-00003			

Note: 2 & 3 metre lengths will be charged pro rata to the 6 metre price + cutting charge.
Metre Rate will be charged for all other cut sizes.

Channel Products

1

Reinforcement

2

Precast

3

FPA/SPA

4

Brickwork

5

Stone

6