



Steel

Flat Head <  
Round Shank <  
Open <

C4C [1.0303]

M		l	No.	
<b>M4</b>	0,5 - 6,0	14,0	10.895.040.600	500
<b>D</b> 6,0	<b>k</b> 0,8	<b>dk</b> 10,0	4 Nm	5200 N
<b>M5</b>	0,5 - 6,0	15,0	10.895.050.600	500
<b>D</b> 7,0	<b>k</b> 1,0	<b>dk</b> 11,0	6 Nm	9500 N

M		l	No.	
<b>M6</b>	0,5 - 6,0	17,5	10.895.060.600	500
<b>D</b> 9,0	<b>k</b> 1,5	<b>dk</b> 13,0	11 Nm	15500 N
<b>M8</b>	0,5 - 7,5	21,5	10.895.080.750	500
<b>D</b> 11,0	<b>k</b> 1,5	<b>dk</b> 16,0	24 Nm	21500 N