

Part No. structure

E3.15.060.032.0


 Color  
 black  
 Bending  
 radius  
 Width  
 Series

## Series E3.15 - snap-open along outer radius

Part No.	$B_i$ [mm]	$B_a$ [mm]	$R$ [mm]	Bending radii	Weight [kg/m]
E3.15.020.	20	32	032 038 048 075	≈ 0,22	
E3.15.040.	40	52	032 038 048 075	≈ 0,25	
E3.15.060.	60	72	032 038 048 075	≈ 0,32	

 The bending radii **038** **075** are available upon request for Series E3.15.020

Delivery time: approx. 6-8 weeks after receipt of order!

Supplement Part No. with required radius. Example: E3.15.060.032.0

0 = standard color, other colors ► page 1.39 · Pitch = 16,7 mm/link - Links/m = 60




## E3 | Series E3.15 | Accessories | Interior Separation

Vertical separator,  
slotted (single)


unassembled E3.15.01

assembled E3.15.11

Vertical separator  
on a strip

unassembled E3.15.01.10

assembled E3.15.11.10



## Vertical separators

Vertical separators are used if a vertical subdivision of the E-Chain® interior is required -

- Subdivision with **vertical separator E3.15.11** (slotted 3 times)
- Five vertical separators altogether on one strip over ten chain links are mounted on the opening crossbars. In this way, controlled chambers are formed, which prevent the sensitive electrical circuit from outage

