

# 气动接头 消声器/转换接头/堵头/泄气阀



气动部品 · 液压配件

## 选型指南

标准	型号		型号		-	No2		型号	
	Code	No.	Code	No1		Code	No.	Code	No.
	<b>CMB</b>	<b>04</b>	<b>GBL</b>	<b>02</b>		<b>03</b>	<b>CBV</b>	<b>02</b>	

### ■消声器

Code	材质
<b>CMB</b>	黄铜
<b>CMSS</b>	不锈钢



### ■消声器



※材质: 铜

型号		螺牙尺寸
Code	No.	
<b>CMB</b> <b>CMSS</b>	<b>01</b>	R1/8
	<b>02</b>	R1/4
	<b>03</b>	R3/8
	<b>04</b>	R1/2
	<b>06</b>	R3/4
	<b>10</b>	R1

型号		配管直径
Code	No.	
<b>GPSF</b>	<b>4</b>	4
	<b>6</b>	6
	<b>8</b>	8
	<b>10</b>	10
	<b>12</b>	12

### ■消声器

Code	材质
<b>CMBS</b>	黄铜
<b>CMBS</b>	不锈钢



### ■消声器



使用流体	空气
最高耐压力	1Mpa
消声器	30dB
环境及流体温度	5~60℃

※材质: 铜

型号		螺牙尺寸
Code	No.	
<b>CMBS</b>	<b>01</b>	R1/8
	<b>02</b>	R1/4
	<b>03</b>	R3/8
	<b>04</b>	R1/2
	<b>06</b>	R3/4
	<b>10</b>	R1

※材质: 塑料

型号		螺牙尺寸
Code	No.	
<b>CPSL</b>	<b>01</b>	R1/8
	<b>02</b>	R1/4
	<b>03</b>	R3/8
	<b>04</b>	R1/2

### ■转换接头



※材质: 铜

型号		No2	左端螺牙尺寸	右端螺牙尺寸
Code	No1			
<b>CBL</b>	<b>01</b>	<b>01</b>	R1/8	R1/8
	<b>02</b>	<b>01</b>	R1/4	R1/8
	<b>02</b>	<b>02</b>	R1/4	R1/4
	<b>03</b>	<b>02</b>	R3/8	R1/4
	<b>03</b>	<b>03</b>	R3/8	R3/8
	<b>04</b>	<b>02</b>	R1/2	R1/4
	<b>04</b>	<b>03</b>	R1/2	R3/8
	<b>04</b>	<b>04</b>	R1/2	R1/2
	<b>06</b>	<b>04</b>	R3/4	R1/2
	<b>06</b>	<b>06</b>	R3/4	R3/4
	<b>08</b>	<b>04</b>	R1	R1/2
	<b>08</b>	<b>06</b>	R1	R3/4
<b>08</b>	<b>08</b>	R1	R1	

### ■转换接头



※材质: 铜

型号		No2	外牙尺寸	内牙尺寸
Code	No1			
<b>CBB</b>	<b>02</b>	<b>01</b>	R1/4	R1/8
	<b>03</b>	<b>02</b>	R3/8	R1/4
	<b>04</b>	<b>02</b>	R1/2	R1/4
	<b>04</b>	<b>03</b>	R1/2	R3/8
	<b>06</b>	<b>04</b>	R3/4	R1/2
	<b>08</b>	<b>04</b>	R1	R1/2
<b>08</b>	<b>06</b>	R1	R3/4	

### ■泄气阀



型号		螺牙尺寸
Code	No.	
<b>CBV</b>	<b>01</b>	R1/8
	<b>02</b>	R1/4
	<b>03</b>	R3/8
	<b>04</b>	R1/2

### ■转换接头



※材质: 铜

型号		No2	左端螺牙尺寸	右端螺牙尺寸
Code	No1			
<b>CBW</b>	<b>01</b>	<b>01</b>	R1/8	R1/8
	<b>02</b>	<b>01</b>	R1/4	R1/8
	<b>02</b>	<b>02</b>	R1/4	R1/4
	<b>03</b>	<b>02</b>	R3/8	R1/4
	<b>03</b>	<b>03</b>	R3/8	R3/8
	<b>04</b>	<b>02</b>	R1/2	R1/4
	<b>04</b>	<b>03</b>	R1/2	R3/8
	<b>04</b>	<b>04</b>	R1/2	R1/2
	<b>06</b>	<b>04</b>	R3/4	R1/2
	<b>06</b>	<b>06</b>	R3/4	R3/4
	<b>08</b>	<b>04</b>	R1	R1/2
	<b>08</b>	<b>06</b>	R1	R3/4
<b>08</b>	<b>08</b>	R1	R1	

### ■堵头



※材质: 铜

型号		螺牙尺寸
Code	No.	
<b>CBD</b>	<b>M5</b>	M5
	<b>01</b>	R1/8
	<b>02</b>	R1/4
	<b>03</b>	R3/8
	<b>04</b>	R1/2
	<b>06</b>	R3/4
<b>08</b>	R1	

使用流体	空气
最高耐压力	1.32Mpa
最高使用压力	0~0.9Mpa
环境及流体温度	0~60℃
材质	铜

真空发生器

真空吸盘

气动接头

气动配件

压头

浮动接头

连接类零件

电磁阀

手动阀

空气调理

气缸

流体控制阀

压力桶

点胶机