

# 针头

## 选型指南

标准	举例	型号
		DPYK-14G-1/4



编号	内径	外径	包装数量	塑座不锈钢精密针头				塑座不锈钢精密弯头针头			
				长1/4英寸	长1/2英寸	长1英寸	长1.5英寸	弯90度, 长1/4英寸	弯90度, 长1/2英寸	弯45度, 长1/4英寸	弯45度, 长1/2英寸
12G	2.25	2.75	100	-	-	-	-	-	-	-	-
13G	2.02	2.4	100	-	-	-	-	-	-	-	-
14G	1.54	1.83	100	DPYK-14G-1/4	DPYK-14G-1/2	DPYK-14G-1	DPYK-1.54G-1.5	DPYKW-14G-1/4	DPYKW-14G-1/2	DPYKN-14G-1/4	DPYKN-14G-1/2
15G	1.36	1.65	100	DPYK-15G-1/4	DPYK-15G-1/2	DPYK-15G-1	DPYK-1.55G-1.5	DPYKW-15G-1/4	DPYKW-15G-1/2	DPYKN-15G-1/4	DPYKN-15G-1/2
18G	0.84	1.27	100	DPYK-18G-1/4	DPYK-18G-1/2	DPYK-18G-1	DPYK-1.58G-1.5	DPYKW-18G-1/4	DPYKW-18G-1/2	DPYKN-18G-1/4	DPYKN-18G-1/2
20G	0.6	0.91	100	DPYK-20G-1/4	DPYK-20G-1/2	DPYK-20G-1	DPYK-20G-1.5	DPYKW-20G-1/4	DPYKW-20G-1/2	DPYKN-20G-1/4	DPYKN-20G-1/2
21G	0.51	0.82	100	DPYK-21G-1/4	DPYK-21G-1/2	DPYK-21G-1	DPYK-21.5G-1.5	DPYKW-21G-1/4	DPYKW-21G-1/2	DPYKN-21G-1/4	DPYKN-21G-1/2
22G	0.41	0.72	100	DPYK-22G-1/4	DPYK-22G-1/2	DPYK-22G-1	DPYK-22G-1.5	DPYKW-22G-1/4	DPYKW-22G-1/2	DPYKN-22G-1/4	DPYKN-22G-1/2
23G	0.34	0.64	100	DPYK-23G-1/4	DPYK-23G-1/2	DPYK-23G-1	DPYK-23G-1.5	DPYKW-23G-1/4	DPYKW-23G-1/2	DPYKN-23G-1/4	DPYKN-23G-1/2
25G	0.26	0.51	100	DPYK-25G-1/4	DPYK-25G-1/2	DPYK-25G-1	DPYK-25G-1.5	DPYKW-25G-1/4	DPYKW-25G-1/2	DPYKN-25G-1/4	DPYKN-25G-1/2
27G	0.21	0.41	100	DPYK-27G-1/4	DPYK-27G-1/2	DPYK-27G-1	DPYK-27G-1.5	DPYKW-27G-1/4	DPYKW-27G-1/2	DPYKN-27G-1/4	DPYKN-27G-1/2
30G	0.16	0.31	100	DPYK-30G-1/4	DPYK-30G-1/2	DPYK-30G-1	DPYK-30G-1.5	-	-	DPYKN-30G-1/4	DPYKN-30G-1/2
32G	0.11	0.23	100	DPYK-32G-1/4	DPYK-32G-1/2	-	-	-	-	-	-
34G	0.06	0.19	100	DPYK-34G-1/4	DPYK-34G-1/2	-	-	-	-	-	-

编号	内径	外径	包装数量	全塑针头	不锈钢针头			不锈钢双针头		
				长1/4英寸	长1/4英寸	长1/2英寸	长1英寸	长1/4英寸	长1/2英寸	长1英寸
12G	2.25	2.75	100	-	DPYKK-12G-1/4	DPYKK-12G-1/2	DPYKK-12G-1	-	-	-
13G	2.02	2.4	100	-	DPYKK-13G-1/4	DPYKK-13G-1/2	DPYKK-13G-1	-	-	-
14G	1.54	1.83	100	DPYK-14G-TT	DPYKK-14G-1/4	DPYKK-14G-1/2	DPYKK-14G-1	-	-	-
15G	1.36	1.65	100	DPYK-15G-TT	DPYKK-15G-1/4	DPYKK-15G-1/2	DPYKK-15G-1	-	-	-
18G	0.84	1.27	100	DPYK-18G-TT	DPYKK-18G-1/4	DPYKK-18G-1/2	DPYKK-18G-1	DPYKKD-18G-1/4	DPYKKD-18G-1/2	DPYKKD-18G-1
20G	0.6	0.91	100	DPYK-20G-TT	DPYKK-20G-1/4	DPYKK-20G-1/2	DPYKK-20G-1	DPYKKD-20G-1/4	DPYKKD-20G-1/2	DPYKKD-20G-1
21G	0.51	0.82	100	DPYK-21G-TT	DPYKK-21G-1/4	DPYKK-21G-1/2	DPYKK-21G-1	DPYKKD-21G-1/4	DPYKKD-21G-1/2	DPYKKD-21G-1
22G	0.41	0.72	100	DPYK-22G-TT	DPYKK-22G-1/4	DPYKK-22G-1/2	DPYKK-22G-1	DPYKKD-22G-1/4	DPYKKD-22G-1/2	DPYKKD-22G-1
23G	0.34	0.64	100	DPYK-23G-TT	DPYKK-23G-1/4	DPYKK-23G-1/2	DPYKK-23G-1	DPYKKD-23G-1/4	DPYKKD-23G-1/2	DPYKKD-23G-1
25G	0.26	0.51	100	DPYK-25G-TT	DPYKK-25G-1/4	DPYKK-25G-1/2	DPYKK-25G-1	DPYKKD-25G-1/4	DPYKKD-25G-1/2	DPYKKD-25G-1
27G	0.21	0.41	100	-	DPYKK-27G-1/4	DPYKK-27G-1/2	DPYKK-27G-1	-	-	-
30G	0.16	0.31	100	-	DPYKK-30G-1/4	DPYKK-30G-1/2	DPYKK-30G-1	-	-	-
32G	0.11	0.23	100	-	DPYKK-32G-1/4	DPYKK-32G-1/2	DPYKK-32G-1	-	-	-
34G	0.06	0.19	100	-	DPYKK-34G-1/4	DPYKK-34G-1/2	DPYKK-34G-1	-	-	-

真空发生器

真空吸盘

气动接头

气动配件

压头

浮动接头

连接类零件

电磁阀

手动阀

空气调理

气缸

流体控制阀

压力桶

点胶机