

Cable management

482.6 mm (19") cable management

Cable routing bars

For structured routing of entire cable bundles, the cable bars may be secured to a variety of different positions inside the enclosure.

Material:

- Support: Sheet steel
- Cable routing bars, connection combs: Plastic

Colour:

- RAL 9005

Supply includes:

- Cable routing bars
- Connection combs

482.6 mm (19") attachment

For horizontal cable routing within the distributor level.

Thanks to their open mounting holes, they can also be retrospectively slotted onto the 482.6 mm (19") system punchings of the mounting level at any time and secured with the existing assembly screws of the installed components.

U	No. of connection combs	Packs of	Model No.
4	2 pc(s).	4 pc(s).	7111.224
1	5 pc(s).	10 pc(s).	7111.214

All-round attachment for universal use

For vertical and horizontal cable routing inside the enclosure or within the distributor level.

U	No. of connection combs	Packs of	Model No.
4	2 pc(s).	4 pc(s).	7111.222
1	5 pc(s).	10 pc(s).	7111.212

Connection comb

For connecting individual cable routing bars into complete systems (included with the supply).

Cable duct

for TS-IT

- High packing density due to U-based cable routing
- Hinged on both sides, removable duct cover
- Suitable for back-to-back baying
- Easily installed with toolless fast assembly on the front and rear 482.6 mm (19") mounting angle of the TS-IT
- Screw-fastening optionally supported

Material:

- Sheet steel, plastic UL 94 V0

Colour:

- RAL 9005

Supply includes:

- Cover and assembly parts
- 4 cable retainers for spare cables

For enclosure height mm	U	Packs of	Model No.
2000	36	1 pc(s).	5502.105
2200	42	1 pc(s).	5502.145

