

Human/machine interface

Handles, external mounting accessories



Handle set VIP

for VIP 6000 with wide frame

For mounting on the corner connectors of the enclosure frame.

Material:

Handle tube:
Extruded aluminium section, natural-anodised
Handle holder:
Die-cast zinc, powder-coated in RAL 7035

Note:

Shorter heights and widths can be achieved by cutting the handle tube to length.



Accessories:

Clipboard, display board
see page 1118.



For horizontal mounting

| With front panel width | Packs of | Model No. CP |
|------------------------|----------|------------------------------|
| 482.6 mm (19") | 1 set | 6101.000 |
| As specified | 1 set | 6101.009¹⁾ |

Supply includes:

2 handle holders,
1 handle tube,
2 screws.

For vertical mounting

| With front panel height | Packs of | Model No. CP |
|-------------------------|----------|------------------------------|
| 7 U | 1 set | 6102.000 |
| As specified | 1 set | 6102.009¹⁾ |

¹⁾ Please additionally state when ordering:

- Number and dimensions of front panel
- Number of cross members/sealing bars
- Order number of your enclosure

Supply includes:

Packs of 4 handle holders,
2 handle tubes,
4 screws.



Handle set

For vertical and horizontal mounting on all surfaces.
Overall length: 420 mm.

Material:

Handle tube: Aluminium, natural-anodised
Conduit holder: Die-cast zinc, RAL 7035

Supply includes:

1 set =
4 conduit holders,
2 handle tubes.

| Packs of | Model No. SZ |
|----------|-----------------|
| 1 set | 2389.000 |



Accessories:

Clipboard, display board
see page 1118.



Handle frame

for operating housing with display panel front

| | CP 6442.500 CP 6462.500 | CP 6552.500 | CP 6662.500 |
|--|----------------------------|-----------------|-----------------|
| Model No. CP | 6191.000 | 6192.000 | 6190.000 |
| Operating housing width (B1) mm | 380 | 500 | 600 |
| Width of the horizontal rectangular tube (B2 = B1 + 48) mm | 428 | 548 | 648 |
| Height of the vertical rectangular tube (H1) mm | 345 | 465 | 299 |
| Hole distance between the assembly holes (H2) mm | 295 | 415 | 249 |

Colour:

RAL 8019

Supply includes:

Rectangular aluminium tube,
plastic corner bracket,
end caps,
assembly parts.

