

Support arm system CP 40/60/120/180

Adaptor

from support arm connection Ø 130 mm to
□ 120 x 65 mm

For external mounting of operating housings with support arm cutout □ 120 x 65 mm and connection console VESA 75/100 to

- Coupling CP 120, 6212.300
- Mounting bracket CP 120, 6212.320
- Angle coupling 90° CP 120, 6212.380
- Pivot with jib, 6016.600
- Pivot for machine-integrated installation, 6016.700

Material:

– Cast aluminium

Colour:

– RAL 7035

Supply includes:

- Seals
- Assembly parts

Height mm	Weight kg	Model No.
40	0.5	6212.500

Technical details:

Available on the Internet



Adaptor

from support arm connection Ø 180 mm to
Ø 130 mm

For mounting between:

- Enclosures with support arm connection Ø 180 mm
- and
- Coupling CP 60/120 for support arm connection Ø 130 mm, 6206.300, 6212.300
 - Mounting bracket CP 60/120 for support arm connection Ø 130 mm, 6206.320, 6212.320
 - Pivot, 6016.600, 6016.700

Material:

– Cast aluminium

Colour:

– RAL 7035

Supply includes:

- Seals
- Assembly parts

Height mm	Weight kg	Model No.
20	0.6	6212.520

Technical details:

Available on the Internet



Adaptor

for Siemens Pro-Panel

For the external mounting of Siemens Simatic

- MP 377 15" Pro
- Thin Client 15" Pro
- Flat-Panel Monitor 15", 19" Pro
- HMI IPC477C 15" Pro

to support arm system

- CP 40, steel
- CP 60/120 with support arm connection □ 120 x 65 mm

Material:

– Aluminium

Colour:

– RAL 7035

Supply includes:

- Seals
- Assembly parts

Weight kg	Model No.
0.3	6206.500

Technical details:

Available on the Internet

