

Stand systems



Comfort Panel Page 124 Optipanel Page 126 Compact Panel Page 133 Operating housing with handle strips Page 130

Pedestal, modular, consisting of:

- Pedestal base plate/cross member
- Support section
- Enclosure connection

Colour:

– RAL 7035

Technical details:

Available on the Internet

Photo shows a configuration

example with equipment not included in the scope of supply

Pedestal, modular

Weight load kg	15	18	35 ¹⁾	35 ¹⁾	Page
[1] Pedestal base plate	Model No.				
Pedestal base plate/cross member	6146.100	6106.100	6106.200	6106.400	
Dimensions mm	Width	400	400	490	600
	Height	10	108	100	205
	Depth	400	400	600	550
[2] Support section	Model No.				
Height-adjustable (adjustment range 732 – 1122 mm)	6146.200	–	–	–	
Closed, length 1000 mm	–	6206.100	6206.100 ¹⁾	6206.100 ¹⁾	
[3] Enclosure connection	Model No.				
Enclosure reinforcement, rigid	–	6106.110	–	–	
Attachment CP 40, steel, for support arm connection □ 90 x 71 mm	6501.070	–	–	–	
Coupling CP 40, steel, for support arm connection □ 90 x 71 mm	6501.050	–	–	–	
Coupling CP 40, steel, for support arm connection □ 120 x 65 mm	6501.130	–	–	–	
Attachment CP 60, for support arm connection Ø 130 mm	–	–	6206.320	6206.320	
Attachment CP 60, for support arm connection □ 120 x 65 mm	–	–	6206.360	6206.360	
Coupling CP 60, for support arm connection Ø 130 mm	–	–	6206.300	–	
Coupling CP 60, for support arm connection □ 120 x 65 mm	–	–	6206.340	–	
Tilt adjustment	6146.300	–	–	–	
Accessories					
Twin castors	6148.000	–	6148.000	■	522
Levelling feet	–	–	4612.000	–	521
Base mounting bracket	–	–	1590.000	–	587

¹⁾ Alternative: Support arm system CP 120 may also be used by simply drilling a hole. Weight capacity 50 kg.