

Base/plinth

Base/plinth TS

Cable chamber

for TS, SE

With integral system punchings for individual system accessories.

Height: 200 mm

Material:

- Sheet steel

Colour:

- RAL 7035

Supply includes:

- Sheet steel trim panels front and rear
- Assembly parts for mounting on the enclosure

For enclosures		Model No.
Width mm	Depth mm	
400	500	8600.455
400	600	8600.465
600	500	8600.655
600	600	8600.665
800	500	8600.855
800	600	8600.865
1200	500	8600.255
1200	600	8600.265



Accessories:

- Side panels for cable chamber, see page 515

Technical details:

Available on the Internet

Side panels

for cable chamber

Height: 200 mm

Material:

- Sheet steel

Colour:

- RAL 7035

Supply includes:

- Assembly parts

For enclosure depth mm	Packs of	Model No.
500	2 pc(s).	8600.510
600	2 pc(s).	8600.520



Transport castors

for base/plinth TS

For locating onto the base/plinth corner piece 100 or 200 mm high.

Load capacity:

- Maximum permissible load per twin castor: static 100 kg

Supply includes:

- 1 set =
4 twin castors, 2 x with, 2 x without locks

Colour:

- RAL 7022

Floor clearance mm	Model No.
100	8800.390



Also required:

- Base/plinth trim panels, side, see page 514

