

Doors/locks

Door variants



Lock components

for TS, TS-IT, SE

For retrofitting a glazed door or sheet steel door in place of a rear panel.

Material:

- Die-cast zinc

Supply includes:

- Assembly screws

Packs of	Model No.
4 pc(s).	8800.040



Glazed door, vented

for TS, TS-IT, SE

With 180° hinges and comfort handle with security lock no. 3524 E. Surface perforated on both sides with air inlet openings > 78 % for optimum air throughput.

Material:

- Door: Sheet steel
- Viewing window: Single-pane safety glass, 3 mm

Surface finish:

- Powder-coated

Colour:

- RAL 7035

Supply includes:

- 4 enclosure hinges
- Assembly parts

For enclosures		Model No.
Width mm	Height mm	
600	2000	7824.201
800	2000	7824.202
800	2200	7824.222

+ Accessories:

- 180° hinge for bayed TS enclosure suites with comfort handle, see page 574



Lockable and adjacent door

for TS, TS-IT, SE

For example, if two 400 mm doors instead of one 800 mm wide door are used to comply with escape routes.

Material:

- Sheet steel

Surface finish:

- Dipcoat-primed, Powder-coated on the outside

Supply includes:

- 2 doors, including tubular door frame, hinges and lock parts

For enclosures		Colour RAL	Model No.
Width mm	Height mm		
800	2000	7035	8801.450

+ Accessories:

- Lock system, see page 564