




Lock inserts

for installation in comfort handle, mini-comfort handle, Ergoform-S standard, folding lever handle

| Installation in |  |  |  |
|---|---|--|--|
| | Lock and push-button inserts | | Semi-cylinder |
| | Comfort handle ⁶⁾ , Mini-comfort handle ⁶⁾ | Comfort handle ⁷⁾ , Mini-comfort handle ⁷⁾ , Ergoform-S standard, Folding lever handle for CM | Comfort handle, Mini-comfort handle, Ergoform-S standard, Folding lever handle for CM |
| Model No. | | | |
| Security lock insert Lock no. 3524 E ¹⁾ | 8611.180 | 2467.000 | - |
| Push-button insert | 8611.190 | 2468.000 | - |
| Push-button and lock insert ¹⁾ | 8611.200²⁾ | 2469.000³⁾ | - |
| to DIN 18 252 ⁴⁾ | - | - | 9785.040 |
| | - | - | 9785.042⁵⁾ |

¹⁾ With two keys

²⁾ Lock no. 12321; no other lock is possible

³⁾ Lock no. 2123; no other lock is possible

⁴⁾ With 3 keys for each lock insert

⁵⁾ Packs of two, simultaneous locking within the same pack, no simultaneous locking for different packs

⁶⁾ For lock inserts

⁷⁾ For semi-cylinders



Folding lever handle

for CM




As the handle does not take up any swing space, due to its folding action, the door surface area may be maximised for installed equipment.

Size:

- Length: 242 mm (with inserted trim panel)
- Width: 50 mm
- Depth: 17.5 mm

Colour:

- Body: Similar to RAL 9005
- Handle: Similar to RAL 9006

| |  |  |  |
|--|---|---|--|
| | for lock inserts | for padlock and lock inserts | with lock insert, lock E1 ¹⁾ |
| | Model No. | | |
| | 5001.060 | 5001.062 | 5001.061 |

Lock inserts, type F

| | | | |
|---------------------------|----------|----------|---|
| 7 mm square | 8611.100 | 8611.100 | - |
| 8 mm square | 8611.110 | 8611.110 | - |
| 7 mm triangular | 8611.120 | 8611.120 | - |
| 8 mm triangular | 8611.130 | 8611.130 | - |
| Screwdriver | 8611.140 | 8611.140 | - |
| Daimler insert | 8611.150 | 8611.150 | - |
| 3 mm double-bit | 8611.160 | 8611.160 | - |
| Fiat | 8611.170 | 8611.170 | - |
| 6.5 mm triangular (CNOMO) | 8611.220 | 8611.220 | - |

Lock and push-button inserts

| | | | |
|--|------------------------|------------------------|---|
| Lock insert, lock no. 3524 E ²⁾ | 2467.000 | 2467.000 | - |
| Push-button insert | 2468.000 | 2468.000 | - |
| Push-button and lock insert ²⁾ | 2469.000 ³⁾ | 2469.000 ³⁾ | - |

Semi-cylinder

| | | | |
|-----------------------------|------------------------|------------------------|---|
| to DIN 18 252 ⁴⁾ | 9785.040 | 9785.040 | - |
| | 9785.042 ⁵⁾ | 9785.042 ⁵⁾ | - |

¹⁾ Only for use with VW, Audi, SEAT, SkodaAuto, supplied without key

²⁾ With two keys

³⁾ Lock no. 2123; no other lock is possible

⁴⁾ With 3 keys for each lock insert

⁵⁾ Packs of two, simultaneous locking within the same pack, no simultaneous locking for different packs

