

Interior installation

Mounting plates



Slide rails

for mounting plate TS

Slides in from the side.

- Attachment of the mounting plate to the slide rails via captive nuts and screws.
- Mounting of the slide rails directly on the enclosure frame, depth-adjustable on a 25 mm pitch pattern

Technical specifications:

- Possible mounting depth T6 -25 mm, refer to the Internet

Material:

- Sheet steel

Surface finish:

- Zinc-plated

Supply includes:

- Assembly parts

For enclosure width mm	Packs of	Model No.
600	2 pc(s).	8802.260
800	2 pc(s).	8802.280
1200	2 pc(s).	8802.220

Mounting plate adjustment bracket

for KS

Infinitely adjustable.

Other equipment can also be installed on a rail system in this way, instead of the mounting plate.

Material:

- Sheet steel

Surface finish:

- Zinc-plated

Supply includes:

- Assembly parts

- W** Enclosure width:
 - 76 mm (1481.000)
 - 104 mm (1491.000)

- H** Enclosure height:
 - 150 mm

For enclosures KS	Packs of	Model No.
1423.500, 1432.500, 1434.500, 1444.500, 1446.500, 1448.500, 1449.500, 1466.500, 1467.500	4 pc(s).	1481.000
1400.500, 1453.500, 1454.500, 1468.500, 1469.500, 1479.500, 1480.500	4 pc(s).	1491.000

