

# LED system light



**Baying systems TS 8** Cat. 34, page 62 **System enclosures SE 8** Cat. 34, page 81 **Compact enclosures AE** Cat. 34, page 46

## Benefits:

- Optimum illumination of the entire enclosure
- Optionally with clip, screw and magnetic attachment
- A configuration to suit every application

## Material:

- Plastic
- Aluminium

## Colour:

- Enclosure: RAL 7016

## Light colour:

- 4000 K (neutral white)

## Supply includes:

- Assembly screws

## Note:

- Connection accessories should be ordered separately
- Information on country-specific versions can be found on the Internet

**Model No. 2500.110 and Model No. 2500.100 available from 1st quarter 2017**

Model No.		2500.310	2500.300	2500.210	2500.200	2500.220	2500.110	2500.100
Output (lumen)		1200	1200	900	900	900	600	400
Length (mm)		437	437	437	437	437	337	262
Motion sensor		■	■	–	–	–	–	–
Rated operating voltage	100 – 240 V AC	■	■	■	■	–	■	■
	24 V DC	–	–	–	–	■	–	–
Equipment	Socket	■	–	■	–	–	–	–
	90° rotating connector	■	■	■	■	■	–	–
	Adjustable light direction	■	■	–	–	–	–	–
	Adjustable light distribution	■	■	■	■	■	–	–
Protection class II			II (all-insulated)			III (SELV)	II (all-insulated)	
Approvals	UL	–	■	–	■	■	–	–
	cUL	–	■	–	■	■	–	–
	CCC	–	■	–	■	–	■	■
	ENEC	■	■	■	■	■	■	■
Installation type	Screw-fastening	■	■	■	■	■	■	■
	Clip attachment	■	■	■	■	■	■	■
	Magnetic attachment to surfaces (accessory)	–	■	–	■	■	■	■
Connection options	Infeed	3-pole	3-pole	3-pole	3-pole	2-pole	2-pole	2-pole
	Through-wiring	3-pole	3-pole	3-pole	3-pole	2-pole	2-pole	2-pole
	Door-operated switch (accessories)	–	–	■	■	■	■	■
Mounting options	Enclosures with a 25 mm pitch pattern	Directly on the profile	Directly on the profile	Directly on the profile	Directly on the profile	Directly on the profile	Directly on the profile	–
	AE	Screw-fastening	With universal bracket					

## Accessories

Universal bracket	2373.000	2373.000	2373.000	2373.000	2373.000	2373.000	2373.000	2373.000
Mounting kit magnet	–	2500.480	–	2500.480	2500.480	2500.480	2500.480	2500.480
Door-operated switch	–	–	2500.460	2500.460	2500.460	2500.460	2500.460	2500.460
Door-operated switch, UL	–	–	–	2500.470	2500.470	–	–	–

## Connection accessories

Infeed, 2-pole	–	–	–	–	2500.410	2500.420	2500.420	
Infeed, 3-pole	2500.400	2500.400	2500.400	2500.400	–	–	–	
Infeed, 3-pole, ENEC, UL	–	2500.500	–	2500.500	–	–	–	
Through-wiring, 2-pole	–	–	–	–	2500.440	2500.450	2500.450	
Through-wiring, 3-pole	2500.430	2500.430	2500.430	2500.430	–	–	–	
Through-wiring, 3-pole, ENEC, UL	–	2500.530	–	2500.530	–	–	–	