

Baying enclosure system VX25



System accessories Page 78 ISV installation modules Page 172

Material and surface finish:

- Enclosure frame: Sheet steel, 1.5 mm, dipcoat-primed
- Roof: Sheet steel, 1.5 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Door: Sheet steel, 2 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Rear panel: Sheet steel, 1.5 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Gland plates: Sheet steel, 1.5 mm, zinc-plated

Colour:

- RAL 7035

Basis of test:

- IEC 61 439-1/-2

Protection category IP to IEC 60 529:

- IP 55

NEMA protection category:

- NEMA 12

Supply includes:

- Enclosure frame
- Door(s) (r/h hinge, may be swapped to opposite side)
- Gland plates
- Roof plate
- Rear panel
- Lock: 3 mm double-bit

Note:

- For 600 mm wide distribution enclosures, please use basic enclosures, see page 54 onwards

Distribution enclosure

Width mm	P. of	850	1100	850	1100	Page
Height mm		2000	2000	2000	2000	
Depth mm		400	400	600	600	
Model No.	1 pc(s).	9666.956	9666.966	9666.916	9666.926	
Weight, approx. kg		111.0	146.0	117.0	156.0	
Door(s)		1	2	1	2	
Also required						
Installation kit	1 pc(s).	9666.912	9666.922	9666.912	9666.922	171
Mounting angle	2 pc(s).	9666.712	9666.712	9666.712	9666.712	178
Depth stay	2 pc(s).	-	9666.732	-	9666.732	178
Accessories						
Base/plinth corner pieces with base/plinth trim panel, front and rear, 100 mm	2 pc(s).	8620.004	8620.006	8620.004	8620.006	85
Base/plinth trim panels, sides, 100 mm	2 pc(s).	8620.031	8620.031	8620.033	8620.033	86
Base/plinth corner pieces with base/plinth trim panel, front and rear, 200 mm	2 pc(s).	2 x 8620.004	2 x 8620.006	2 x 8620.004	2 x 8620.006	85
Base/plinth trim panels, sides, 200 mm	2 pc(s).	8620.031	8620.031	8620.033	8620.033	86
Levelling feet	4 pc(s).	4612.000	4612.000	4612.000	4612.000	91
Side panels, screw-fastened, sheet steel	2 pc(s).	8104.245	8104.245	8106.245	8106.245	96
Baying bracket, internal	6 pc(s).	8617.500	8617.500	8617.500	8617.500	106
Baying block, internal	6 pc(s).	8617.501	8617.501	8617.501	8617.501	106
Baying connector, external	6 pc(s).	8617.502	8617.502	8617.502	8617.502	106
Roof plate for cable entry glands	1 pc(s).	9681.594	9681.514	9681.596	9681.516	136
Cable entry glands	14 x M25/32	1 pc(s).	9665.750	9665.750	9665.750	137
	2 x M25/32/40, 1 x M32/40/50, 2 x M40/50/63	1 pc(s).	9665.760	9665.760	9665.760	137
	With sealing membranes 32 x Ø 7 – 16 mm, 4 x Ø 10 – 20 mm, 3 x Ø 14 – 26 mm	1 pc(s).	9665.770	9665.770	9665.770	137
	With entry fittings up to Ø 66 mm	1 pc(s).	9665.780	9665.780	9665.780	137
	Solid	4 pc(s).	9665.785	9665.785	9665.785	137