

# Compartment configuration

Form 1-4

## Functional space side panel modules

### For internal compartmentalisation

- Side divider panel for compartments, for locating into the TS pitch pattern.
- Prepared for the location of mounting brackets for horizontal compartment dividers or mounting plates
- Two TS system punchings allow the use of additional TS accessories.
- The side panel modules for reduced compartment depth and an auxiliary construction using TS punched rails 17 x 17 mm can be used to provide a separate enclosure space in the side panel area, e.g. for the provision of a busbar system.

### Material:

Sheet steel, zinc-plated, passivated, 1.5 mm

### Supply includes:

Assembly parts.



### Accessories:

- TS 17 x 17 mm punched rails and connector pieces, see page 656.
- Gland plates, see page 346.

### A) Without gland plate<sup>1)</sup>

Height mm	For compartment depth	Packs of	Model No. SV
100	425 mm	6	9673.051
150	425 mm	6	9673.055
200	425 mm	6	9673.052
100	600 mm	6	9673.061
150	600 mm	6	9673.065
200	600 mm	6	9673.062
600	600 mm	2	9673.066
100	800 mm	6	9673.081
150	800 mm	6	9673.085
200	800 mm	6	9673.082
600	800 mm	2	9673.086

<sup>1)</sup> Version without gland plate has pre-punched cable entries M40.

### B) With gland plate<sup>1)</sup>

Height mm	For compartment depth	Packs of	Model No. SV
150	425 mm	6	9673.155
200	425 mm	6	9673.152
150	600 mm	6	9673.165
200	600 mm	6	9673.162
600	600 mm	2	9673.166
150	800 mm	6	9673.185
200	800 mm	6	9673.182
600	800 mm	2	9673.186

<sup>1)</sup> Version with plastic plate has pre-punched knockouts for cable entry.

## Functional space side panel modules

### for cable connection space

For mounting a Maxi-PLS cable connection bar system

### Material:

Sheet steel, zinc-plated, passivated, 2 mm

### Supply includes:

Assembly parts.

Height mm	Packs of	Model No. SV	
		For enclosure depth	
		600 mm	800 mm
450	2	9673.069	9673.089
Suitable for cable connection busbar system			
Maxi-PLS	Number of poles		
1600/2000	3-pole	■	■
1600/2000	4-pole	■	■
3200	3-pole	■	■
3200	4-pole	–	■



### Also required:

- 2 functional space side panel modules with height 150 mm, see page 345.
- End support, see page 328.

