



**Busbar system** Cat. 34, page 212 **OM adaptors** Cat. 34, page 219

**Material:**

- Polyamide
- Fire protection corresponding to UL 94

**Colour:**

- RAL 7035

**Note:**

- For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adaptor combinations (OM adaptors/ supports)

**Approvals:**

- UL 4248-1
- UL 4248-4
- UL 4248-8

**Further technical information:**

Available on the Internet

## Rated operating current max. 30 – 60 A

Fuse type (class)		CC	J	J	Page
Rated operating current max. A		30	30	60	
Rated operating voltage V, ~		600, 3~	600, 3~	600, 3~	
Number of poles		3-pole	3-pole	3-pole	
Fuse standard		UL 248-4	UL 248-8	UL 248-8	
Fuse size mm		10 x 38	21 x 57	27 x 60	
Voltage, indicator light V		110 - 600	110 - 600	110 - 600	
Connection of round conductors mm <sup>2</sup>		0.75 - 25	1.5 - 50	2.5 - 50	
Connection of round conductors		AWG 8 - 18	AWG 1 - 18	AWG 1 - 14	
Width mm		54	108	120	
Height mm		81	115	118	
<b>Model No.</b>		<b>9345.005</b>	<b>9345.015</b>	<b>9345.035</b>	
	Packs of	4 pc(s).	2 pc(s).	2 pc(s).	