


# TopTherm wall-mounted cooling units "Blue e"

## Output class 1500 W

Model No.	Packs of	3305.500	3305.510	3305.540	3305.600	3305.640	Page
Material	Sheet steel	■	■	■	–	–	
	Stainless steel	–	–	–	■	■	
Colour	RAL 7035	■	■	■	–	–	
<b>Total cooling output 50 Hz L35 L35 to DIN EN 14511 kW</b>		<b>1.6</b>	<b>1.6</b>	<b>1.6</b>	<b>1.6</b>	<b>1.6</b>	
Total cooling output 50/60 Hz L35 L35 kW		1.6 / 1.76	1.6 / 1.76	1.6 / 1.61	1.6 / 1.76	1.6 / 1.61	
Total cooling output 50/60 Hz L35 L50 kW		1.25 / 1.37	1.25 / 1.37	1.33 / 1.35	1.25 / 1.37	1.33 / 1.35	
Rated operating voltage V, ~, Hz		230, 1~, 50/60	115, 1~, 50/60	400, 3~, 50 460, 3~, 60	230, 1~, 50/60	400, 3~, 50 460, 3~, 60	
Width (B) mm		400	400	400	400	400	
Height (H) mm		950	950	950	950	950	
Depth (T) mm		260	260	260	260	260	
Rated current max. A		5.5 / 5.8	11.5 / 12.5	2.5 / 2.8	5.5 / 5.8	2.5 / 2.8	
Start-up current A		12 / 14	26 / 28	12.2 / 11.3	12 / 14	12.2 / 11.3	
Pre-fuse A		16	–	–	16	–	
Transformer circuit-breaker A		–	14...20	–	–	–	
Motor circuit-breaker A		–	–	6.3...10	–	6.3...10	
Power consumption P <sub>el</sub> 50/60 Hz L35 L35 kW		0.87 / 0.98	0.87 / 0.98	0.9 / 1.08	0.87 / 0.98	0.9 / 1.08	
Power consumption P <sub>el</sub> 50/60 Hz L35 L50 kW		1.03 / 1.15	1.03 / 1.15	1.06 / 1.25	1.03 / 1.15	1.06 / 1.25	
Operating temperature range		+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	
Setting range		+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	
Energy efficiency ratio (EER) 50 Hz L35 L35 to DIN EN 14511		1.83	1.83	1.83	1.83	1.83	
Refrigerant g		R134a, 500	R134a, 500	R134a, 500	R134a, 500	R134a, 500	
Permissible operating pressure (p. max.) bar		28	28	28	28	28	
Air throughput of fans (unimpeded air flow), internal circuit / external circuit m <sup>3</sup> /h		800 / 900	800 / 900	800 / 900	800 / 900	800 / 900	
Weight kg		41.0	46.0	42.0	41.0	42.0	
<b>Accessories</b>							
Filter mats	3 pc(s).	3286.400	3286.400	3286.400	3286.400	3286.400	369
Metal filters	1 pc(s).	3286.410	3286.410	3286.410	3286.410	3286.410	370
Door-operated switch	1 pc(s).	4127.010	4127.010	4127.010	4127.010	4127.010	639

Accessories



Therm software

see page 385