

# Air/water heat exchangers



Climate control accessories Page 369 Chillers Page 361 Therm software Page 385

**Colour:**

– RAL 7035

**Protection category IP to IEC 60 529:**

– IP 55

**Cooling medium:**

– Water (see Internet for specifications)

**Supply includes:**

- Fully wired ready for connection (plug-in terminal strip)
- Drilling template
- Sealing and assembly parts

**Note:**

- Integral non-return valve for version with e-Comfort controller

**Approvals:**

Available on the Internet

**Performance diagrams:**

Available on the Internet

**Technical details:**

Available on the Internet

## Output class 300 – 500 W, wall-mounted

Model No.	Packs of	3212.024	3212.115	3212.230	3363.100	3363.500	Page
Water-carrying parts	Copper/brass (Cu/CuZn)	■	■	■	■	■	
Temperature control	Basic controller (factory setting +35°C)	–	–	–	■	–	
	e-Comfort controller (factory setting +35°C)	–	–	–	–	■	
<b>Total cooling output L35 W10, 200 l/h kW</b>		<b>0.3</b>	<b>0.3</b>	<b>0.3</b>	–	–	
<b>Total cooling output L35 W10, 400 l/h kW</b>		–	–	–	<b>0.5</b>	<b>0.5</b>	
Rated operating voltage V, ~, Hz		24 (DC)	115, 1~, 50/60	230, 1~, 50/60	230, 1~, 50/60	230, 1~, 50/60	
Width mm		150	150	150	280	280	
Height mm		300	300	300	550	550	
Depth mm		85	85	85	120	120	
Power consumption P <sub>el</sub> 50/60 Hz W		26	26 / 30	23 / 27	37 / 38	37 / 38	
Rated current max. A		1.2	0.23 / 0.24	0.11 / 0.13	0.18 / 0.18	0.18 / 0.18	
Pre-fuse A		2	2	2	4	4	
Operating temperature range		+1°C...+70°C	+1°C...+70°C	+1°C...+70°C	+1°C...+70°C	+1°C...+70°C	
Setting range		–	–	–	+20°C...+55°C	+20°C...+55°C	
Water inlet temperature		+1°C...+30°C	+1°C...+30°C	+1°C...+30°C	+1°C...+30°C	+1°C...+30°C	
Water connection	½" connector sleeve	–	–	–	■	■	
	G ¾" external thread	–	–	–	■	■	
	¾" connector sleeve	■	■	■	–	–	
Permissible operating pressure (p. max.) bar		1 - 10	1 - 10	1 - 10	1 - 10	1 - 10	
Air throughput of fans (unimpeded air flow) m³/h		250	260 / 300	280 / 310	290 / 345	290 / 345	
Weight kg		3.2	3.2	3.2	8.0	8.0	

**Accessories**

		3301.610	3301.610	3301.610	3301.612	3301.612	377
Condensate hose	1 pc(s).	3301.610	3301.610	3301.610	3301.612	3301.612	377
Door-operated switch	1 pc(s).	4127.010	4127.010	4127.010	4127.010	4127.010	639
Toroidal transformer, primary connection 115 V/400 V	1 pc(s).	–	–	3201.960	see page	see page	382
Fitting G ¾"	2 pc(s).	–	–	–	3201.900	3201.900	378
Flow regulator valve		see page	see page	see page	see page	see page	378
Digital enclosure internal temperature display and thermostat	1 pc(s).	3114.200	3114.200	3114.200	–	–	379
SK BUS system	1 pc(s).	–	–	–	–	3124.100	382
Interface board	1 pc(s).	–	–	–	–	3124.200	381