

SERIES 62NY

“TR-ROLL” POLYURETHANE WHEELS WITH POLYAMIDE 6 CENTER, ALSO AVAILABLE WITH WITH ERGONOMIC ROUND PROFILE



Wheel description

“TR-ROLL” polyurethane wheels, hardness 75 Shore A, excellent sliding and elasticity, good resistance to wear and tear.

Hub

The housing is obtained by moulding and contains ball bearings series Z. The hub is available also without bearings.

Diameters: 100-160 mm

Carrying capacity: 230-400 daN



Fittings with swivel, fixed and swivel with brake brackets



Standard duty brackets type NL

Max. carrying capacity 300 daN – available diameters 100-165 mm
Top plate fastening. Front-locking brake systems



Medium duty brackets type M

Max. carrying capacity 400 daN – available diameters 160 mm
Top plate fastening. Adjustable front-locking brake



Medium-heavy duty brackets type P

Max. carrying capacity 400 daN – available diameters 100-160 mm
Top plate fastening. Front-locking and adjustable rear-locking brake systems

Uses

Environments

The series is suitable for use in industrial environments for carrying medium-heavy loads, including with mixed outdoor-indoor use. Can be used at speeds of up to 6 km/h; possibility of using for mechanised towing. Typical usage: trolleys for automotive industry. *Usage temperatures:* from -20 °C to +70 °C

Floors



Handling

