


## SERIES 63



### VULKOLLAN® WHEELS, FORGED STEEL CENTRE, SWIVEL TOP PLATE BRACKET TYPE NL

#### Wheel description




**Tread:** Vulkollan® polyurethane tread; hardness 93 +/-2 Shore A.

**Centre:** forged steel.

**Hub:** the housing is obtained by moulding and turning and contains ball bearings series Z.

#### Bracket description



#### Standard duty bracket type NL (max. carrying capacity 400 daN)

- 1) **Plate:** electrolytically galvanised steel plate
  - 2) **Fork:** electrolytically galvanised steel plate
  - 3) **Ball Racing Ring:** electrolytically galvanised steel plate
  - 4) **King Pin:** incorporated in top plate and cold riveted
  - 5) **Swivel actions:** double ring of greased balls
  - 6) **Dust seal:** orange polyethylene
- Finishing:** electrolytic galvanisation  
**Fitting:** top plate