


SERIES 72



SIGMA ELASTIC RUBBER WHEELS ALUMINIUM CENTRE SWIVEL TOP PLATE BRACKET TYPE EEG MHD

Wheel description




Tread: Sigma Elastic rubber tread; hardness 70 +/-3 Shore A.

Centre: aluminium.

Hub: The housing is obtained by moulding and contains ball bearings series Z.

Bracket description

EEG Medium Heavy Duty bracket (max. load capacity 900 daN)



- 1) **Plate:** forged steel with integrated pin
 - 2) **Fork:** drawn sides electrowelded to the flange
 - 3) **Swivel actions:** axial ball bearing and taper roller bearing
 - 4) **Lubricator**
 - 5) **Nut anti-loosening system**
- Finish:** electrolytic galvanisation
Fitting: top plate