

SERIES 22

STANDARD RUBBER WHEELS WITH POLYPROPYLENE CENTRE



Wheel description

Standard non-marking rubber tread; hardness 80 Shore A. Polypropilene centre.

Hub

The hub is available with plain bore and with roller bearing.

Diameters: 80-200 mm

Carrying capacities: 65-225 daN

Fittings with swivel, fixed and swivel with brake brackets



Standard duty brackets type NL - NLX

Max. carrying capacity 400 daN – available diameters 80-300 mm

Models available: with top plate fastening, with bolt hole

Suitable brakes: front-locking and central (hexagonal) brake systems

Uses

Environments

Suitable for humid environments where medium-harsh chemicals are present; not suitable for applications where organic solvents, chlorinated substances, hydrocarbons and mineral oils are present; it can be fitted under trolleys and charts of any kind, with light and standard carrying capacity. It can be used also for outdoor applications.

Typical usage: trolleys for indoor and outdoor industrial handling, luggage trolleys.

Usage temperatures: from -20°C a +60°C

Floors



Handling

