


SERIES 68



SOLID POLYAMIDE 6 WHEELS SWIVEL TOP PLATE BRACKET TYPE EE HD WITH REAR ADJUSTABLE BRAKE

Wheel description




Tread: solid polyamide 6 wheels.

Hub: the housing is obtained by moulding and turning and contains ball bearings.


Bracket description

EE Heavy Duty bracket (max. load capacity 2500 daN)



- 1) **Plate:** forged steel with integrated pin
 - 2) **Fork:** drawn sides electrowelded to the flange
 - 3) **Swivel actions:** axial ball bearing and taper roller bearing
 - 4) **Lubricator**
 - 5) **Nut anti-loosening system**
- Finish:** dark green powder coating
Fitting: top plate

Brake description



Rear adjustable brake

Double-action brake that locks the wheel and the castor at the same time. The brake is efficient and easy to use: a simple top-to-bottom movement using the tip of the foot on two independent pedals is all that's needed to engage and release the lock quickly and smoothly. Locking force can be adjusted using an M8 socket screw.