

SERIES 76

POLYAMID 6 SOLID TRANSPALLET ROLLERS



Roller description

Solid polyamide 6 transpallet roller, excellent rolling resistance, abrasion and impact resistance.

Hub

The housing is obtained by moulding and turning and contains ball bearings series Z. The hub is available also without bearings

Hubs: 40-82 mm

Carrying capacities: 700-1200 daN

Uses

Environments

Suitable for humid environments with harsh chemicals; not suitable for application where concentrated organic acids or strong mineral acids are present.

Usage temperatures: from -30 °C to +80 °C

Floors



Handling

