

Angular expansion joint DN 185

Oper. pressure [bar]: 6 (external)

Oper. temp. range [K]: 90 ÷ 310

Oper. travel ranges (max.)
- angular [°] : ± 3

Weight (max) [Kg] : 14.6

Spring rates (max.)
- angular [N m/°] : 120

Operating fluids : LOX

Bellows material : SS 316 L

Application : A5 EPC LOX tank penetration

Status : Qualified for flight

