



Threaded rod

M5, M6, M8, M10, M12

Nr.	A	B	g
22777	M5	20	1
22778	M5	40	2
22779	M5	60	3
22780	M5	80	4
22781	M5	100	4
22782	M5	120	5

Nr.	A	B	g
21719	M6	25	2
21720	M6	50	3
21721	M6	75	5
21722	M6	100	6
21723	M6	125	8
21724	M6	150	9

Nr.	A	B	g
21725	M8	25	2
21726	M8	50	6
21727	M8	75	8
21728	M8	100	10
21729	M8	125	14
21730	M8	150	16

Nr.	A	B	g
21775	M10	25	4
21776	M10	50	8
21777	M10	75	12
21778	M10	100	18
21779	M10	125	22
21780	M10	150	26

Nr.	A	B	g
21781	M12	25	6
21782	M12	50	12
21783	M12	75	18
21784	M12	100	24
21785	M12	125	32
21786	M12	150	38

