


轴用挡圈



1 代号 RRAJB	M 材质 弹簧钢	H 硬度 44-52HRC	S 表面处理 ACP(磷酸盐保护膜)
-----------------------------	--------------------	-------------------------	------------------------------

▲符合ASME/ANSI B18.27.4-6-2017标准

视角标准：第一视角



1代号 - **2**公称代号
RRAJB - 15

1 代号	2 公称代号	挡圈								参考		适用孔(参考)				
		d ₂		d ₁	t		(m)	d ₀		d ₄	d ₅	d ₃		c		b
		尺寸	公差		尺寸	公差		尺寸	公差			尺寸	公差	尺寸	公差	
RRAJB	6	5.6		8	0.5	±0.03	1.2	-	-	8.9	6	5.7	0 -0.04	0.6	+0.1 0	
	7	6.5	+0.1 -0.2	9.3	0.6	±0.04	1.4	-	-	10.3	7	6.7	0	0.7		
	8	7.4		10.6	0.7		1.6	-	-	11.7	8	7.6	-0.06	0.8		
	9	8.4		12	0.8		1.8	-	-	13.1	9	8.6		0.95		
	10	9.3	±0.15	13.3			2			14.5	10	9.6	0 -0.09			
	11	10.2		14.4			2.1			16	11	10.5				
	12	11.1		15.5			2.2			17.2	12	11.5			1.15	
	13	12		16.6	1	±0.05	2.3	1.2		18.4	13	12.4				
	14	12.9		17.5			2.3		±0.3	19.4	14	13.4	0			
	15	13.8	±0.18	18.6			2.4			20.6	15	14.3	-0.11		1.5	
	16	14.7		19.7			2.5			21.8	16	15.2				
	17	15.7		20.9			2.6			23	17	16.2				
	18	16.7		21.9			2.7			24.2	18	17				
	19	17.5		23.1			2.8			25.4	19	18				
	20	18.5		24.3			2.9			27	20	19				
	21	19.5		25.5	1.2		3	1.5		28	21	20			1.35	
	22	20.5		26.5			3			29	22	21				
	24	22.2		28.6			3.2			31.5	24	22.9	0			
	25	23.2	±0.2	29.8		±0.06	3.3			33	25	23.9	-0.21		+0.14 0	
	26	24.2		31			3.4			34	26	24.9				
	28	25.9		33.1			3.6			36.5	28	26.6				
	30	27.9		34.1	1.5		3.7	1.8	±0.4	37.5	30	27.6			1.65	
	32	29.6		35.3			3.9			38.5	32	28.6				
	34	31.5		39.7			4.1			41	34	30.3				
	35	32.2	±0.25	40.6			4.2			43.5	35	33				
	36	33.2		41.6	1.75		4.2			45	36	34				
	38	35.2		44			4.4			46	38	36				
	40	37		46.2			4.6	2		48	40	38	0 -0.25	1.9		
	42	38.5		48.1			4.8			51	42	39.5				
	45	41.5		51.3			4.8			54	45	42.5				
48	44.5	±0.4	55.1			5.3			57	48	45.5			2		
50	45.8		56.8	2	±0.07	5.5			63	50	47					
52	47.8		59			5.6		±0.5	65	52	49					
55	50.8		62.6			5.9			69	55	52			2.2		
58	53.8		66			6.1	2.5		72	58	55	0 -0.3				
60	55.8	±0.45	68.4			6.3			75	60	57					
62	57.8		70.8			6.5			77	62	59			2.7		
63	58.8		72			6.6			78	63	60					
65	60.8		74.4	2.5	±0.08	6.8	3		81	65	62					

K1
圆柱销
油嘴
平键
挡圈
开口销