


**Tuleja prowadząca**

Leader pin bushing

**TPE**



**Uwaga: Dostępne także z powłoką DLC.**  
**W celu zamówienia skontaktuj się z nami.**  
 Note: Available with DLC coating. Contact FCPK for details.

d	d1	d2	s	f	l	L	NR KAT.	NR KAT.
10	14	16	3	3	15	12		TPE-10012
					20	17		TPE-10017
					25	22		TPE-10022
					30	27		TPE-10027
					39	36		TPE-10036
					46	46		TPE-10046
						56		TPE-10056
66		TPE-10066						
14/15	20	25	6	9	21	12	TPE-14012	TPE-15012
					26	17	TPE-14017	TPE-15017
					31	22	TPE-14022	TPE-15022
					36	27	TPE-14027	TPE-15027
					45	36	TPE-14036	TPE-15036
					55	46	TPE-14046	TPE-15046
					56	56	TPE-14056	TPE-15056
						66	TPE-14066	TPE-15066
						76	TPE-14076	TPE-15076
						86	TPE-14086	TPE-15086
						96	TPE-14096	TPE-15096
116	TPE-14116	TPE-15116						
18/20	26	31	6	9	26	17	TPE-18017	TPE-20017
					31	22	TPE-18022	TPE-20022
					36	27	TPE-18027	TPE-20027
					45	36	TPE-18036	TPE-20036
					55	46	TPE-18046	TPE-20046
					65	56	TPE-18056	TPE-20056
					75	66	TPE-18066	TPE-20066
					76	76	TPE-18076	TPE-20076
						86	TPE-18086	TPE-20086
						96	TPE-18096	TPE-20096
						116	TPE-18116	TPE-20116
						136	TPE-18136	TPE-20136

## Tuleja prowadząca

Leader pin bushing

# TPE

d	d1	d2	s	f	l	L	NR KAT.	NR KAT.
22/24	30	35	6	9	26	17	TPE-22017	TPE-24017
					31	22	TPE-22022	TPE-24022
					36	27	TPE-22027	TPE-24027
					45	36	TPE-22036	TPE-24036
					55	46	TPE-22046	TPE-24046
					65	56	TPE-22056	TPE-24056
					75	66	TPE-22066	TPE-24066
					85	76	TPE-22076	TPE-24076
					95	86	TPE-22086	TPE-24086
					96	96	TPE-22096	TPE-24096
						116	TPE-22116	TPE-24116
						136	TPE-22136	TPE-24136
						156	TPE-22156	TPE-24156
30/32	42	47	6	9	31	22	TPE-30022	TPE-32022
					36	27	TPE-30027	TPE-32027
					45	36	TPE-30036	TPE-32036
					55	46	TPE-30046	TPE-32046
					65	56	TPE-30056	TPE-32056
					75	66	TPE-30066	TPE-32066
					85	76	TPE-30076	TPE-32076
					95	86	TPE-30086	TPE-32086
					105	96	TPE-30096	TPE-32096
					116	116	TPE-30116	TPE-32116
						136	TPE-30136	TPE-32136
						156	TPE-30156	TPE-32156
						176	TPE-30176	TPE-32176
196	TPE-30196	TPE-32196						
40/42	54	60	10	12	48	36	TPE-40036	TPE-42036
					58	46	TPE-40046	TPE-42046
					68	56	TPE-40056	TPE-42056
					78	66	TPE-40066	TPE-42066
					88	76	TPE-40076	TPE-42076
					98	86	TPE-40086	TPE-42086
					108	96	TPE-40096	TPE-42096
					128	116	TPE-40116	TPE-42116
					136	136	TPE-40136	TPE-42136
						156	TPE-40156	TPE-42156
						176	TPE-40176	TPE-42176
						196	TPE-40196	TPE-42196
					50/52	66	71	10
78	66	TPE-50066	TPE-52066					
88	76	TPE-50076	TPE-52076					
98	86	TPE-50086	TPE-52086					
108	96	TPE-50096	TPE-52096					
128	116	TPE-50116	TPE-52116					
136	136	TPE-50136	TPE-52136					
	156	TPE-50156	TPE-52156					
	176	TPE-50176	TPE-52176					
	196	TPE-50196	TPE-52196					
	216	TPE-50216	TPE-52216					
	236	TPE-50236	TPE-52236					
256	TPE-50256	TPE-52256						