


Tuleja prowadząca samosmarująca

Self-lubricating guide bushing

TPG



Mat: Brąz aluminiowy + grafit.
Aluminium bronze + graphite.

d	d1	d2	s	f	L	NR KAT.	NR KAT.
9/10	14	16	3	5	12	TPG-09012	TPG-10012
					17	TPG-09017	TPG-10017
					22	TPG-09022	TPG-10022
					27	TPG-09027	TPG-10027
					36	TPG-09036	TPG-10036
					46	TPG-09046	TPG-10046
					56	TPG-09056	TPG-10056
14/15	20	25	6	6	17	TPG-14017	TPG-15017
					22	TPG-14022	TPG-15022
					27	TPG-14027	TPG-15027
					36	TPG-14036	TPG-15036
					46	TPG-14046	TPG-15046
					56	TPG-14056	TPG-15056
					66	TPG-14066	TPG-15066
					76	TPG-14076	TPG-15076
18/20	26	31	6	8	86	TPG-14086	TPG-15086
					17	TPG-18017	TPG-20017
					22	TPG-18022	TPG-20022
					27	TPG-18027	TPG-20027
					36	TPG-18036	TPG-20036
					46	TPG-18046	TPG-20046
					56	TPG-18056	TPG-20056
					66	TPG-18066	TPG-20066
					76	TPG-18076	TPG-20076
86	TPG-18086	TPG-20086					
96	TPG-18096	TPG-20096					

Tuleja prowadząca samosmarująca

Self-lubricating guide bushing

TPG

d	d1	d2	s	f	L	NR KAT.	NR KAT.
22/24	30	35	6	8	22	TPG-22022	TPG-24022
					27	TPG-22027	TPG-24027
					36	TPG-22036	TPG-24036
					46	TPG-22046	TPG-24046
					56	TPG-22056	TPG-24056
					66	TPG-22066	TPG-24066
					76	TPG-22076	TPG-24076
					86	TPG-22086	TPG-24086
					96	TPG-22096	TPG-24096
					116	TPG-22116	TPG-24116
30/32	42	47	6	8	136	TPG-22136	TPG-24136
					27	TPG-30027	TPG-32027
					36	TPG-30036	TPG-32036
					46	TPG-30046	TPG-32046
					56	TPG-30056	TPG-32056
					66	TPG-30066	TPG-32066
					76	TPG-30076	TPG-32076
					86	TPG-30086	TPG-32086
					96	TPG-30096	TPG-32096
					116	TPG-30116	TPG-32116
40/42	54	60	10	10	136	TPG-30136	TPG-32136
					46	TPG-40046	TPG-42046
					56	TPG-40056	TPG-42056
					66	TPG-40066	TPG-42066
					76	TPG-40076	TPG-42076
					86	TPG-40086	TPG-42086
					96	TPG-40096	TPG-42096
					116	TPG-40116	TPG-42116
					136	TPG-40136	TPG-42136
					156	TPG-40156	TPG-42156
196	TPG-40196	TPG-42196					