

十字孔圆头螺丝 (盘头十字)


code
5天发货

选型指南

举例	型号	-	L
标准	Code M	-	L
	LSS28Z 6	-	12



类型	Code	材质	表面处理
十字孔圆头螺丝	LSS28Z	SWCH	镀锌
	LSS28B	SUS304	-
十字孔圆头小螺丝	LSS29S		



型号		L	螺距	D	H
Code	M				
LSS28Z	2.5	4 6 8 10 12	0.45	5	2.1
	3	4 6 8 10 12 16 18 20 25 30 35 40	0.5	5.6	2.4
	4	5 6 8 10 12 14 16 20 25 30	0.7	8	3.1
	5	8 10 12 14 16 20 25 30 35 40	0.8	9.5	3.7
	6	8 10 12 14 16 20 25 30 35 40 45 50	1	12	4.6

型号		L
Code	M	
LSS28B	1.6	2 3 4 5 6 8 10 12 14 16
	2	2 3 4 5 6 8 10 12 14 16 18 20 25
	2.5	3 4 5 6 8 10 12 14 16 18 20 25 30
	3	4 5 6 8 10 12 14 16 18 20 25 30 35 40 45 50
	3.5	6 8 10 12 14 16 20 25 35
	4	6 8 10 12 14 16 18 20 25 30 35 40 45 50 55 60 65 70 75 80
	5	6 8 10 12 14 16 18 20 25 30 35 40 45 50 55 60 65 70 75 80 85 90 95 100
	6	8 10 12 14 16 18 20 25 30 35 40 45 50 55 60 65 70 75 80 85 90 95 100
	8	10 12 14 16 18 20 25 30 35 40 45 50 55 60 65 70 75 80 85 90 95 100
	10	12 14 16 18 20 25 30 35 40 45 50 55 60 65 70 75 80 85 90 95 100

Code	M	螺距	D	H
LSS28B	1.6	0.35	3.2	1.3
	2	0.4	4	1.6
	2.5	0.45	5	2.1
	3	0.5	5.6	2.4
	3.5	0.6	7	2.6
	4	0.7	8	3.1
	5	0.8	9.5	3.7
	6	1.0	12	4.6
	8	1.25	16	6
	10	1.5	20	7.5

型号		L
Code	M	
LSS29S	2	3 4 5 6 8 10 12 14 16 18 20 22 25
	2.5	3 4 5 6 8 10 12 14 16 18 20 22 25 30
	3	4 5 6 8 10 12 14 16 18 20 22 25 30 35 40 45 50
	4	5 6 8 10 12 14 16 18 20 22 25 30 35 40 45 50 55 60 65 70 75 80
	5	6 8 10 12 14 16 18 20 22 25 30 35 40 45 50 55 60 65 70 75 80 85 90 95 100
	6	8 10 12 14 16 18 20 22 25 30 35 40 45 50 55 60 65 70 75 80 85 90 95 100
	8	10 12 14 16 18 20 22 25 30 35 40 45 50 55 60 65 70 75 80 85 90 95 100

Code	M	螺距	D	H
LSS29S	2	0.4	3.5	1.4
	2.5	0.45	4.5	1.8
	3	0.5	5.5	2.15
	4	0.7	7	2.75
	5	0.8	9	3.45
	8	1.25	14	5.4

小零件

圆线弹簧

拉簧

扭簧

矩形弹簧

扣环

平键

销子

磁铁

小零件

密封圈

垫圈

轴环

精密垫片

螺丝

螺母
垫圈