

Human/machine interface

Front assembly



1



2



3

Mounting kit

for Comfort Panel

For the installation of aluminium front panels, command panels and keyboards.

Supply includes:

CP 6058.800, CP 6053.800:
20 each of retaining claws, captive nuts, screws, nuts and sealing washers.

CP 6053.300:
6 medium retaining claws, 8 short retaining claws

CP 6053.400:
4 long retaining claws, 6 short retaining claws

1 6058.800, 6053.800

2 6053.300

3 6053.400

For drilled holes/bolts/front panel mounting from behind

Thread	Model No. CP
M4	6058.800
M5	6053.800

For screw clamp

For installing:	Model No. CP
Siemens Sinumerik: OP 010, OP 010 C, OP 012, TP 012, OP 015, OP 015 A, MCP 483 C, MCP 483, PP 012, PP 012 extension, MCP, KB 483 C, Querty 19" Siemens Simatic: Panel PC 477, 577, 677, 677B: 12.1" keys, 12.1" touch, 15.1" keys, 15.1" touch, 19" touch Panel PC 877: 12.1" keys, 15.1" keys, 15.1" touch, 19" touch, TP 270 6", TP 277 6" MP 270 B 6" MP 370 15" touch, MP 377 15" touch, MP 370 12" touch, MP 377 12" touch, MP 377 19" touch B & R: Automation Panel Panel PC Siemens Simatic: OP 270 6", OP 277 6" TP 270 10", MP 270 B 10" touch, MP 277 10" key, MP 377 10" touch, OP 270 10", MP 270 B 10" keys, MP 370 12" key, MP 377 12" key	6053.300
Siemens Simatic: OP 270 6", OP 277 6" TP 270 10", MP 270 B 10" touch, MP 277 10" key, MP 377 10" touch, OP 270 10", MP 270 B 10" keys, MP 370 12" key, MP 377 12" key	6053.400

Cross member

for VIP 6000 and Optipanel

For horizontal and/or vertical division of the Command Panel front.
With mounting channel on both sides to accommodate mounting kits.

Material:

Extruded aluminium section

Supply includes:

2 retaining claws,
2 screws with washers,
2 trim sections.



Front panel width mm	Model No. CP	
	for VIP 6000 ²⁾	for Optipanel
482.6 (19")	6015.000	6386.000
As specified ¹⁾	6015.009	6386.009

¹⁾Please specify width/height of front panel.

²⁾Trim type and trim colour, see page 219.

Please state on the order.

+ Accessories:

Mounting kit,
see page 1121.

Detailed drawing,

for VIP 6000,
see page 1210.
for Optipanel,
see page 1204.