

# Door/locks

## Door variants



### Sheet steel door

#### for DK-TS

To replace existing doors. With 180° hinges and swivel handle with security lock no. 3524 E, in exchange for comfort handle.

**Material:**  
Sheet steel

**Colour:**  
RAL 7035

**Protection category:**  
IP 55 to EN 60 529/09.2000

**Supply includes:**  
Assembly parts.

For enclosures		Model No. DK
Width mm	Height mm	
600	2000	<b>7824.205</b>
800	1200	<b>7824.127</b>
800	2000	<b>7824.207</b>
600	2200	<b>7824.225</b>
800	2200	<b>7824.227</b>



#### Accessories:

Comfort handle, see page 947.  
180° hinge for bayed TS enclosure suites with comfort handle, see page 962.



### Sheet steel door, vented

#### for DK-TS

With 180° hinges and swivel handle with security lock no. 3524 E, in exchange for comfort handle. For optimum air throughput in network enclosures with a high proportion of active components. Slotted surface (SWG-6.7 hexagon) with air inlet openings >78 %.

**Material:**  
Sheet steel

**Colour:**  
RAL 7035

**Supply includes:**  
Assembly parts.

For enclosures		Model No. DK
Width mm	Height mm	
600	1200	<b>7824.123<sup>1)</sup></b>
600	1800	<b>7824.183</b>
800	1200	<b>7824.124</b>
800	1800	<b>7824.184</b>
600	2000	<b>7824.203</b>
800	2000	<b>7824.204</b>
600	2200	<b>7824.223</b>
800	2200	<b>7824.224</b>

<sup>1)</sup> Delivery times available on request.



#### Accessories:

Comfort handle, see page 947.  
180° hinge for bayed TS enclosure suites with comfort handle, see page 962.

Door variants

B  
7.4



### Glazed door, vented

#### for DK-TS

With 180° hinges and comfort handle with security lock no. 3524 E. For optimum air throughput in network enclosures with a low proportion of active components.

**Material:**  
Sheet steel, spray-finished  
Viewing window of 3 mm single-pane safety glass, side slotted surfaces (SWG-6.7 hexagon) for air inlet.

**Colour:**  
RAL 7035

**Supply includes:**  
Assembly parts.

For enclosures		Model No. DK
Width mm	Height mm	
600	1200	<b>7824.121<sup>1)</sup></b>
600	1800	<b>7824.181<sup>1)</sup></b>
800	1800	<b>7824.182<sup>1)</sup></b>
600	2000	<b>7824.201</b>
800	2000	<b>7824.202</b>
600	2200	<b>7824.221</b>
800	2200	<b>7824.222</b>

<sup>1)</sup> Delivery times available on request.



#### Accessories:

180° hinge for bayed TS enclosure suites with comfort handle, see page 962.